



Specifications:

规格:
Voltage rating: 500V AC/DC
额定电压: 500V AC/DC
Current rating: 1A AC/DC
额定电流: 1A AC/DC
Withstanding voltage: 1000V AC/minute
耐压电压: 1000V AC/分钟
Temperature range: -40°C ~ +105°C
温度范围: -40°C ~ +105°C
Insulation resistance: ≥1000MΩ
绝缘电阻: ≥1000MΩ
Contact resistance: ≤20mΩ
接触电阻: ≤20mΩ
After environment testing: ≤30mΩ
环境试验后: ≤30mΩ

X9127 H I - XX X - PT XX

- ① Series No.
- ② Category: H-HSG
- ③ Appearance type: I-HSG+hardware
- ④ Row No.-Pin No.: XX-Single ROW
- ⑤ Plug the Pin & Special No.:
- ⑥ Material: PT-PBT 94V-0
- ⑦ Color: RD-purplish red
RE-Red Color

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
4	8.45	2.54	16	23.69	17.78
6	10.99	5.08	18	26.23	20.32
8	13.53	7.62	20	28.77	22.86
10	16.07	10.16	22	31.31	25.40
12	18.61	12.70	24	33.85	27.94
14	21.15	15.24	26	36.39	30.48

X9127HI-XX-PTRE	Red	PBT UL 94V-0	Brass	Tin-Plated
X9127HI-XX-PTRD	Purplishj			
PART NO	Color	Material	Material(Pin)	Finish(Pin)

广东星河科技股份有限公司

生 日期

文件工程章

REVISIONS

DATE REVISED APPROVED

UNSPECIFIED TOLERANCES

www.helixkb.com www.helixkb.cn

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWNN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	1.27 mm Crimp Style Connectors
APPD	DATE	SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO., LIMITED			X9127HI-XX-PTXXX
		WEIGHT	SHEET
		1.0g	1/1
		REVISION	A0