



Specifications:

规格:  
 Voltage rating:50V AC/DC  
 额定电压: 50V AC/DC  
 Current rating:1A AC/DC  
 额定电流: 1A AC/DC  
 Contact Resistance:≤20MΩ  
 接触电阻: ≤20MΩ  
 Insulation Resistance:≥100MΩ  
 绝缘电阻:≥100MΩ  
 Dielectric strength:250V AC/minute  
 耐压: 250V AC/minute  
 Plug-in force: ≤3N(per pin)  
 插入力: ≤3N (per pin)  
 Plug-out force:≥0.3N (per pin)

X1254 H-XX-N0  
 ① ② ③ ④

- ① Series No
- ② Category:H-HSG
- ③ Row No:-Pin XX-02P-15P
- ④ Material:N0-PA66 94V-0

Circuit s	Dinansin mm		Circuit s	Dinansin mm	
	A	B		A	B
2	1.25	5.6	10	11.25	15.60
3	2.50	6.85	11	12.50	16.85
4	3.75	8.10	12	13.75	18.10
5	5.00	9.35	13	15.00	19.35
6	6.25	10.60	14	16.25	20.60
7	7.50	11.85	15	17.50	21.85
8	8.75	13.10	—	—	—
9	10.00	14.35	—	—	—



MARK

X1254H-XX-N0	PA66 UL 94V-0	X1254W	Tin-Plated	X1254H
PART NO	Material	Material(pin)	Finish(Pin)	Suitable XKB Terminal

广东星坤科技股份有限公司

生数 日期

文件工程章

REVISIONS

UNSPECIFIED TOLERANCES

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn

DSND		DATE		SCALE: N/A	MODEL TYPE: Wire to board connector
DWN		DATE		VIEW:	PART NO.:
CHKD		DATE		UNIT: mm/in	1.25mm Crimp Style Connectors
APPD		DATE		SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO., LIMITED					X1254H-XX-N0
WEIGHT			SHEET		REVISION
			1/1		A0