



Specifications:  
 规格:  
 Voltage rating:250V AC/DC  
 额定电压: 250V AC/DC  
 Current rating:1A AC/DC  
 额定电流: 1A AC/DC  
 Withstanding voltage:500V AC/minute  
 耐受电压: 500V AC/分钟  
 Temperature range:-40°C-+105°C  
 温度范围: -40°C-+105°C  
 Insulation resistance: 1000MΩ min  
 绝缘电阻: 1000MΩ Min  
 Contact resistance:20mΩ Max  
 接触电阻: 20mΩ Max

X2001 H3 -2xXX- PT V01  
 ① ② ③ ④ ⑤

- Series No
- Category:H3-Two piece with bow button
- Row No.Pin No:2xXX-2x03P-2x30P
- Material:PT-PBT Glass Fiber UL94V-0
- Plating:V01-Gold Flash

Poles	DIM A	DIM B
2x03	11.20	4.00
2x04	13.20	6.00
2x05	15.20	8.00
2x06	17.20	10.00
2x07	19.20	12.00
2x08	21.20	14.00
2x09	23.20	16.00
2x10	25.20	18.00
2x11	27.20	20.00
2x12	29.20	22.00
2x13	31.20	24.00
2x14	33.20	26.00
2x15	35.20	28.00
2x17	39.20	32.00
2x18	41.20	34.00
2x20	45.20	38.00
2x22	49.20	42.00
2x25	55.20	48.00
2x30	65.20	58.00

X2001H3-2xXX-PTV01	PBT Glass Fiber	Brass	X2001W-B
PART NO	Material	Material(Pin)	Suitable XKB Wafer

DSND	SCALE: N/A	MODEL TYPE: 2.0mm IDC Connector
DWN	VIEW:	PART NO.: X2001H3-2xXX-PTV01
CHKD	UNIT: mm/in	DWG NO.: X-X2001H3-2xXX-PTV01
APPD	SIZE: A4	WEIGHT



XKB INDUSTRIAL PRECISION CO., LIMITED

SHEET	REVISION
1/1	A0

ANGULAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	

广东星坤科技股份有限公司

DATE	REVISIONS
日期	REVISIONS

文件工程章