

Specifications:

规格:

Voltage rating:400V AC/DC

额定电压: 400V AC/DC

Current rating:14A AC/DC

额定电流: 14A AC/DC

Withstanding voltage:1800V AC/minute

耐受电压: 1800V AC/分钟

Temperature range:-40°C-+105°C


温度范围: -40°C-+105°C

Insulation resistance:1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:10mΩ Max

接触电阻: 10mΩ Max



1.Series No

2.Category:T-Tterminal

3.Category:TP-Phosphor Bronze Ter
TH-High Conductive copper alloy Ter

4.Plating:Tin Plated 80-120u"Min

5.Type: TypeA ; TypeB

X3501T-TXSN-A	AWG#20-22	2.20	2.20	2.10	2.33	X3501H
X3501T-TXSN-B	AWG#16-18	2.80	2.80	2.63	2.90	Suitable XKB Housing
PART NO	Wire Range	DIM A	DIM B	DIM C	DIM D	

ANGLAR	±5°
ΔX	L ≤ 4 ±0.2
ΔX	4 < L ≤ 16 ±0.3
ΔX	16 < L ≤ 63 ±0.4
MARK	L > 63 ±0.5
UNSPECIFIED TOLERANCES	



DSND	SCALE: N/A	MODEL TYPE: 3.5mm Crimp Style Connector
DWN	VIEW:	PART NO.: X3501T-TXSN-X
CHKD	UNIT: mm/in	DWG NO.: X-X3501T-TXSN-X
APPD	SIZE: A4	WEIGHT
XKB INDUSTRIAL PRECISION CO., LIMITED		SHEET
		1/1
		REVISION
		A0