




2 CKT




3 CKT




4 CKT




5 CKT






6 CKT



7 CKT



8 CKT



Specifications:

规格:

Voltage rating:400V AC/DC

额定电压: 400V AC/DC

Current rating: 14A AC/DC

额定电流: 14A AC/DC

Withstanding voltage:1800V AC/minute

耐受电压: 1800V AC/分钟

Temperature range:-40°C-+105°C

温度范围: -40°C-+105°C


Insulation resistance:1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:15mΩ Max

接触电阻: 15mΩ Max

X3501 HL - XX - N0 X



1.Series No

2.Category:HL-Matching rubber shell row line lock

3.Row No.Pin No:XX-02~08P

4.Material:N0-Nylon66 UL94V-0

5.Color:BK-Black ; N-Natural

Poles	Dimensions(mm)	
	A	B
02	3.50	8.20
03	7.00	11.70
04	10.50	15.20
05	14.00	18.70
06	17.50	22.20
07	21.00	25.70
08	24.50	29.20

X3501HL-XX-N0BK	Black	Nylon66	X3501H-XXA / X3501H-XXB
X3501HL-XX-N0N	Natural		X3501H-2xXXA / X3501H-2xXXB
PART NO	Material	Material	Suitable XKB Housing

DSND		SCALE: N/A	MODEL TYPE: 3.5mm Crimp Style Connector
DWN		VIEW:	PART NO.: X3501HL-XX-N0X
CHKD		UNIT: mm/in	DWG NO.: X-X3501HL-XX-N0X
APPD		SIZE: A4	



XKB INDUSTRIAL PRECISION CO.,LIMITED

广东星坤科技股份有限公司

ΔX	日期
ΔX	日期
ΔX	日期
MARK	DESCRIPTION

文件工程章

					ANGLAR	±5°
					L ≤ 4	±0.2
					4 < L ≤ 16	±0.3
					16 < L ≤ 63	±0.4
					L > 63	±0.5

REVISIONS				UNSPECIFIED TOLERANCES		
www.helloxkb.com	www.helloxkb.cn	www.xk-dg.cn				