



技术参数

Technology Parameters

- Frequency Range 频率范围: 0 - 11GHz
- Impedance 特性阻抗: 50 Ω
- Insulation Resistance 绝缘电阻: 500MΩ Min
- Dielectric Withstanding Voltage 耐压: 200V AC 1Min
- Inner Contact Resistance 接触电阻 20m Ω Max
- Outer Contact Resistance 接触电阻.10 m Ω Max
- Voltage Standing wave Ra>HVSWR) 电压驻波比: 1.3 Max
- Mechanical Durably ; 机械寿命: 100 Cycles
- Relative Humidity 相对湿度: 95% R.H.Max
- Operating Temperature 工作温度: -40 ~ +85 度

new		2015/5/3	A	瀚源	
ECN BO.		DESCRIPTION.	DATE.	REV.	
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2	SCALE: 3:1
Mikey	Tom	Jerry	PART NAME	RF0412G112B	UNLESS OTHERWISE SPECIFIED, TOLERANCE: X. ±0.25 X.x ±0.20 X.xx ±0.15 ANGULAR ±3°
			MODEL NAME	X-RF0412G112B	
			3RD ANGLE PROJ	HanElectricity Co.,LTD	