



Specifications:  
 规格:  
 Voltage rating:250V AC/DC  
 额定电压: 250V AC/DC  
 Current rating:3A AC/DC  
 额定电流: 3A AC/DC  
 Withstanding voltage:1000V AC/minute  
 耐受电压: 1000V AC/分钟  
 Temperature range:-40℃-+125℃  
 温度范围: -40℃-+125℃  
 Insulation resistance:1000MΩ min  
 绝缘电阻: 1000MΩ Min  
 Contact resistance:20mΩ Max  
 接触电阻: 20mΩ Max

X2508 T - P SN - A  
 ① ② ③ ④ ⑤


- 1.Series No
- 2.Category:T-Terminal
- 3.Material:P-Phosphoric bronze
- 4.Plating:SN-Tin Plated
- 5.Special No.



A-A



B-B



C-C

X2508T-PSN-A	Phosphoric bronze	AWG#22~28	X2508H-A
PART NO	Material	Wrie Range	Suitable XKB Housing

DSND	SCALE: N/A	MODEL TYPE: 2.5mm Crimp Style Connector
DWN	VIEW:	PART NO.: X2508T-PSN-A
CHKD	UNIT: mm/in	DWG NO.: X-X2508T-PSN-A
APPD	SIZE: A4	

Δx					ANGLAR	±5°
Δx					L ≤ 4	±0.2
Δx					4 < L ≤ 16	±0.3
MARK	DESCRIPTION	DATE	REVISED	APPROVED	16 < L ≤ 63	±0.4
					L > 63	±0.5
REVISIONS						UNSPECIFIED TOLERANCES



XKB INDUSTRIAL PRECISION CO., LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0