



SPECIFICATIONS


- 1、Current Rating: 1A AC, DC
- 2、Voltage Rating: 50V AC, DC
- 3、Temperatuer Range: -25°C~+85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 100MΩ Min
- 6、Withstanding Voltang: 500V AC/minute
- 7、Material:Phosphoric bronze Tin-plated
- 8、Applicable Wire Sizes:AWG#28~32#



SEC:A-A



SEC:B-B



1002T-PSN-E	Phosphoric bronze	1002W-E	1002H-E
PART NO	Material	Suitable Wafer	Suitable Housing

—		new		2015/5/3		A		瀚源		
ECN BO.		DESCRIPTION.		DATE.		REV.				
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2		SCALE: 3:1				
Mikey	Tom	Jerry	PART NAME	1002T-PSN-E	UNLESS OTHERWISE SPECIFIED,TOLERANCE:	X.	±0.25			
			MODEL NAME	H-1002T-PSN-E		X.x	±0.20	X.xx	±0.15	ANGULAR
			3RD ANGLE PROJ	HanElectricity Co.,LTD				FILE.NO.		