



- SPECIFICATIONS**
- 1、Current Rating: 1A AC, DC
 - 2、Voltage Rating: 50V AC, DC
 - 3、Temperatuer Range: -25°C~+85°C
 - 4、Contact Resistance: 20mΩ Max
 - 5、Insulation Resistance: 100MΩ Min
 - 6、Withstanding Voltang: 500V AC/minute
 - 7、Material:Phosphoric bronze Tin-plated
 - 8、Applicable Wire Sizes:AWG#26~32#



A-A



B-B

1251T-PSN	Phosphor Bronze	1251W	1251H
PART NO	Material	Suitable Wafer	Suitable Housing

—		new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2		SCALE: 3:1			
Mikey	Tom	Jerry	PART NAME	1251T-PSN	UNLESS OTHERWISE SPECIFIED,TOLERANCE:	X.	±0.25		
			MODEL NAME	H-1251T-PSN		X.x	±0.20		
			3RD ANGLE PROJ	HanElectricity Co.,LTD				ANGULAR	±0.15