



适应基板厚度: 1.2mm~1.6mm
 温度范围: -25℃~85℃
 额定电压: 250V AC/DC
 额定电流: 1A
 绝缘电阻: ≥1000MΩ
 耐压: 800V AC/minute

15	23	21.00	24.00
14	21.5	19.50	22.50
13	20	18.00	21.00
12	18.5	16.50	19.50
11	17	15.00	18.00
10	15.5	13.50	16.50
9	14	12.00	15.00
8	12.5	10.50	13.50
7	11	9.00	12.00
6	9.5	7.50	10.50
5	8	6.00	9.00
4	7.5	4.50	7.50
3	6	3.00	6.00
2	4.5	1.50	4.50
Pin	DIM.A	DIM.B	DIM.C

1502H-XXP	PA66 UL94V-0	1502W	1502T
PART NO	Material	Suitable Wafer	Suitable Terminal

new		2015/5/3	A	瀚源		
ECN BO.		DESCRIPTION.	DATE.		REV.	
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2	SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	1502H-XXP	UNLESS OTHERWISE SPECIFIED,TOLERANCE:	X. ±0.25
			MODEL NAME	H-1502H-XXP		X.x ±0.20
			3RD ANGLE PROJ	HanElectricity Co.,LTD		X.xx ±0.15
FILE.NO.						