



技术要求

1. 温度范围 (Temperature range): $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
2. 额定电压 (Voltage rating): 250V.AC/DC
3. 额定电流 (Current rating): 3A
4. 接触电阻 (Contact resistance): $\leq 0.02\ \Omega$
5. 绝缘电阻 (Insulation resistance): $\geq 1000\text{M}\ \Omega$
6. 耐压 (Withstand voltage): 1000V.AC/1分钟 (Minute)

线数 poles	型号 Type	尺寸 Dimensions (mm)		
		A	B	C
2	2510-2A	2.54	2.40	5.08
3	2510-3A	5.08	4.94	7.62
4	2510-4A	7.62	7.48	10.16
5	2510-5A	10.16	10.02	12.70
6	2510-6A	12.70	12.56	15.24
7	2510-7A	15.24	15.10	17.78
8	2510-8A	17.78	17.64	20.32
9	2510-9A	20.32	20.18	22.86
10	2510-10A	22.86	22.72	25.40
11	2510-11A	25.40	25.26	27.94
12	2510-12A	27.94	27.80	30.48
13	2510-13A	30.48	30.34	33.02
14	2510-14A	33.02	32.88	35.56
15	2510-15A	35.56	35.42	38.10
16	2510-16A	38.10	37.96	40.64

2510WV-XXP	PA66 UL94V-0	Brass	2510H
PART NO	Material	Material(Pin)	Suitable Housing

—		new		2015/5/3		A		瀚源	
ECN NO.		DESCRIPTION.		DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2		SCALE: 3:1			
Mikey	Tom	Jerry	PART NAME	2510WV-XXP	UNLESS OTHERWISE SPECIFIED, TOLERANCE:	X.	±0.25		
			MODEL NAME	H-2510WV-XXP		X.x	±0.20		
			3RD ANGLE PROJ	HanElectricity Co.,LTD				X.xx	±0.15
			FILE NO.						