



|             |               |          |               |                   |
|-------------|---------------|----------|---------------|-------------------|
| 8821WV-XXDP | Nylon UL94V-0 | Brass    | Tin Plated    | 8821H-D           |
| Series No.  | Material      | Material | Metal plating | Mate with Housing |

**Specifications:**

规格:

- 1.Voltage rating:250VAC/DC  
额定电压: 250V AC/DC
- 2.Current rating:3A AC/DC  
额定电流: 3A AC/DC
- 3.Withstanding voltage:1000V AC/minute  
耐受电压: 1000V AC/分钟
- 4.Temperature range: -25°C-+85°C  
温度范围: -25°C-+85°C
- 5.Insulation resistance:1000MΩ MIN  
绝缘电阻: 1000MΩ MIN
- 6.Contact resistance:10mΩ Max  
接触电阻: 10mΩ Max

| Circuits | Dimensions |       |       |       |
|----------|------------|-------|-------|-------|
|          | A          | B     | C     | D     |
| 2        | 2.50       | 7.50  | 6.00  | 3.00  |
| 3        | 5.00       | 10.00 | 8.50  | 3.00  |
| 4        | 7.50       | 12.50 | 11.00 | 3.80  |
| 5        | 10.00      | 15.00 | 13.50 | 6.30  |
| 6        | 12.50      | 17.50 | 16.00 | 8.80  |
| 7        | 15.00      | 20.00 | 18.50 | 11.30 |
| 8        | 17.50      | 22.50 | 21.00 | 13.85 |
| 9        | 20.00      | 25.00 | 23.50 | 16.40 |
| 10       | 22.50      | 27.50 | 26.00 | 18.90 |
| 11       | 25.00      | 30.00 | 28.50 | 21.40 |
| 12       | 27.50      | 32.50 | 31.00 | 23.90 |
| 13       | 30.00      | 35.00 | 33.50 | 26.50 |
| 14       | 32.50      | 37.50 | 36.00 | 29.00 |
| 15       | 35.00      | 40.00 | 38.50 | 31.50 |
| 16       | 37.50      | 42.50 | 41.00 | 34.00 |

|          |         |          |                |                        |                                       |             |
|----------|---------|----------|----------------|------------------------|---------------------------------------|-------------|
| ECN BO.  |         | new      |                | 2015/5/3               | A                                     | 瀚源          |
| DESIGNED | CHECKED | APPROVAL | DRAWING NUMBER | DATE.                  | REV.                                  |             |
| MIKEY    | TOM     | JERRY    | PART NAME      | 8821WV-XXDP            | UNLESS OTHERWISE SPECIFIED,TOLERANCE: | X. ±0.25    |
|          |         |          | MODEL NAME     | H-8821WV-XXDP          |                                       | X.x ±0.20   |
|          |         |          | 3RD ANGLE PROJ | HanElectricity Co.,LTD |                                       | X.xx ±0.15  |
|          |         |          |                |                        |                                       | ANGULAR ±3° |
|          |         |          |                |                        |                                       | FILE.NO.    |