



CIRCUIT DIAGRAM





SMD REFLOW PATTERN



SPECIFICATION

Contact Rating	50mA, 12V DC
Contact Resistance	100m max
Insulation Resistance	100m min. 500V DC
Dielectric Strength	250V AC/1minute
Travel	1.3mm
Operating Temp	-30 85
Storage Temp	-30 80



⑤	Terminal	—	2	Brass (0.30t)	Plating silvering	—
④	Contact	—	1	F.ag/Sus	Natural	—
③	Base	—	1	Lcp	—	—
②	Cover	—	1	Lcp	—	—
①	Keystake	—	1	Lcp	—	—
ITEM	PAPT NAMF	TER.NO	QTY	MATERIAL	FINISHING	REMARK

—		new		2015/5/3	A	
ECN BO.		DESCRIPTION.		DATE.	REV.	
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2		SCALE: 3:1
Mikey	Tom	Jerry	PART NAME	TS-1199A26050	UNLESS OTHERWISE SPECIFIED, TOLERANCE:	X. ±0.25
			MODEL NAME	TS-1199A26050		X.x ±0.20
			3RD ANGLE PROJ	HANYONES TECH CO.,LTD		X.xx ±0.15
						ANGULAR ±3'
						FILE. NO.