



P.C.B LAYOUT

**Specifications:**  
 规格:  
**Voltage rating:**250V AC/DC  
 额定电压: 250V AC/DC  
**Current rating:**2A AC/DC  
 额定电流: 2A AC/DC  
**Withstanding voltage:**1000V AC/minute  
 耐受电压: 1000V AC/分钟  
**Temperature range:**-40°C-+105°C  
 温度范围: -40°C-+105°C  
**Insulation resistance:**≥1000MΩ  
 绝缘电阻: ≥1000MΩ  
**Contact resistance:**≤20mΩ  
 接触电阻: ≤20mΩ  
**Material:**PA6T UL94V-0  
 材质: PA6T UL94V-0  
**Plating Category:**1U"Gold  
 镀层: 1U"Gold  
**Wave soldering temperature:**255±5°C, 10S  
 波峰焊温度: 255±5°C, 10S

X4621 W R - 2xXX I - C40 D28  
 ① ② ③ ④ ⑤ ⑥ ⑦

1. Series No
2. Category:W-Wafer
3. Welding Board Angle:R-Stright 90°
4. Row No.Pin No:2xXX-2x01~2x40P
5. Plastic Height:l=2.0mm
6. Pin Length:C=4.0mm
7. Pin Length:D=2.8mm

X4621WR-2xXXI-C40D28	PA6T	Brass	X4621F
PART NO	Material	Material(Pin)	Suitable XKB Female

广东星坤科技股份有限公司

文件工程章

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
Δ生					ANGLAR ±5°
Δ数					L ≤ 4 ±0.2
Δ*					4 < L ≤ 16 ±0.3
					16 < L ≤ 63 ±0.4
					L > 63 ±0.5



DSND		SCALE: N/A	MODEL TYPE: 2.0mm BTB Connector
DWN		VIEW:	PART NO.: X4621WR-2xXXI-C40D28
CHKD		UNIT: mm/in	DWG NO.: X-X4621WR-2xXXI-C40D28
APPD		SIZE: A4	WEIGHT SHEET REVISION 1/1 A0

XKB INDUSTRIAL PRECISION CO., LIMITED