








REV.	ECN. NO.	APPD.
A		
序号	品名	材质
①	1.0E压胶态 (H2.0)	LCP UL94V-0 本色
②	0.5E压端子 (H2.0)	铜合金/表面镀锡 镀金
③	0.5E压后盖 (H2.0)	LCP UL94V-0 黑色
④	0.5E压垫片 (H2.0)	铜合金/表面镀锡



CKT	DIMA	DIMB	DIMC
4	3.00	5.02	8.04
5	4.00	6.02	9.04
6	5.00	7.02	10.04
7	6.00	8.02	11.04
8	7.00	9.02	12.04
9	8.00	10.02	13.04
10	9.00	11.02	14.04
11	10.00	12.02	15.04
12	11.00	13.02	16.04
13	12.00	14.02	17.04
14	13.00	15.02	18.04
15	14.00	16.02	19.04
16	15.00	17.02	20.04
17	16.00	18.02	21.04
18	17.00	19.02	22.04
19	18.00	20.02	23.04
20	19.00	21.02	24.04
21	20.00	22.02	25.04
22	21.00	23.02	26.04
23	22.00	24.02	27.04
24	23.00	25.02	28.04
25	24.00	26.02	29.04
26	25.00	27.02	30.04
27	26.00	28.02	31.04
28	27.00	29.02	32.04
29	28.00	30.02	33.04
30	29.00	31.02	34.04

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -25°C~85°C.
3. 额定电压: 50V, AC/DC(等效).
4. 接触电阻: ≤0.03Ω.
5. 绝缘电阻: ≥500MΩ.
6. 产品料号:

NO OF CKT (产品PIN数) → XX X X
 Plating(电镀方式) → T T T T
 0: 端子全穿锡
 1: 端子全金(G/F OVERALL)
 5: 端子半金锡

Packing(包装方式)
 T: TUBE 管装
 R: TAPE & REEL 卷装

HW10200—XX X X

X.	± 0.30	X°	± 5°	UNITS	mm	NAME(INTENDED USE)	PART NO.(INTENDED USE)	TITLE:
X	± 0.20	X°	± 2°	MATL				MINTRON CO.,LTD.
.XX	± 0.10	.XX°	± 1°	FINISH				FPC1.0 后压卧式 (H=2.0)
.XXX	± 0.05	.XXX°	± 0.5°					
FPC CONNECTOR		QTY		APPD: SUNNY		DR: ZOE		DWG NO.: HW10200-XXXX
				CHKD: LISA		2019-07-11		SCALE: 1/1
								SHEET: 1/1
								REV: A