



**04XN-1XP607-F 1**

1:Au 1U"  
6:Au 30U"

1:SPCC 5:BRASS  
S:Scrolls F:Flat

B:Black O: Orange  
G: Green W: White BL:Blue

1:PBT  
2:PA6T  
3:PA9T  
4:LCP

规格说明:Specifications:

电气特性:Electrical:

- 1.额定电流: Current Rating  
1.5A/contact terminal
- 2.额定电压:Voltage Rating  
30VDC
- 3.接触阻抗:Contact Resistance  
30 milliohms MAX
- 4.耐电压:Dielectric Withstanding Voitage  
500 VAC AT Sea Levlo
- 5.绝缘阻抗:Lnsulation Resistance:  
1000MEGA ohms MIN

物理性能:Mechanical:

- 1.插拔力; Cnnector Mate and Unmate Force  
Mate force:3.57kgf(MAX)  
Unmate force:1.02kgf(MIN)
- 2.端子保持力:Terminal Retenion  
1.2kgf(MIN)

原材料:Matorial:

- 1.塑胶:Housing:  
Hing Temperature Tnermaplastics,  
UL 94V-0 PBT White/Black
- 2.端子:Contact:Copper Alloy C2680
- 3.外壳:Shell: SPCC

电镀:Finish:

- 1.端子:Contact: Plated Gold in Mating Area  
Tin On Solder Talls
- 2.外壳:Shell:  
Nickel Plating

—		new		2015/5/3	A	瀚源
ECN BO.		DESCRIPTION.		DATE.	REV.	
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2		SCALE: 3:1
Mikey	Tom	Jerry	PART NAME	04XN-1XP607-F1	UNLESS OTHERWISE SPECIFIED,TOLERANCE:	X. ±0.25
			MODEL NAME	04XN-1XP607-F1		X.x ±0.20
			3RD ANGLE PROJ	HanElectricity Co.,LTD		X.xx ±0.15
					ANGULAIR	±3
					FILE.NO.	