

规格说明:Specifications:

电气特性:Electrical:

- 1.额定电流: Current Rating  
1.5A/contact terminal
- 2.额定电压: Voltage Rating  
30V DC
- 3.接触阻抗:Contact Resistance  
30 milliohms MAX
- 4.耐电压:Dielectric Withstanding Voitage:  
500 V AC AT Sea Level
- 5.绝缘阻抗:Lnsulation Resistance:  
1000MEGA ohms MIN

物理性能:Mechanical:



- 1.插拔力: Cnector Mate and Unmate Force  
Mate force:3.57kgf(MAX)  
Unmate force:1.02kgf(MIN)
- 2.端子保持力: Terminal Retenion  
1.2kgf(MIN)

原材料:Matorial:

- 1.塑胶:Housing:  
Hing Temperature Tnermaplastics,  
UI 94V-0 PBT White/Black
- 2.端子:Contact:Copper Alloy C2680
- 3.外壳:Shell: Copper Alloy C2680/SPCC

电镀:Finish:

- 1.端子:Contact: Plated Gold in Mating Area;  
Tin On Solder Talls
- 2.外壳:Shell:  
Nickel Plating



PCB LAYOUT

04XN-1XVZ15-S1

- 1:Au 1U"
- 6:Au 30U"
- 1:SPCC 5:BRASS
- S:Scrolls F:Flat
- B:Black O: Orange
- G: Green W: White BL:Blue
- 1:PBT
- 2:PA6T
- 3:PA9T
- 4:LCP

new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	04XN-1XVZ15-S1	UNLESS OTHERWISE SPECIFIED, TOLERANCE:	X.	±0.25
			MODEL NAME	04XN-1XVZ15-S1		X.x	±0.20
			3RD ANGLE PROJ	HanElectricity Co.,LTD		X.xx	±0.15
						ANGULAIR	±3
						FILE.NO.	