

NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL:

HOUSING: THERMOPLASTIC SEAL: SILICONE RUBBER

2. MODIFICATIONS: N/A

3. SPECIFICATIONS:

- 3.1 CURRENT RATING: 25 AMPS
- 3.2 OPERATING TEMPERATURE: -55°C TO +125°C
- 3.3 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC. 3.4 INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 25°C.
- 3.5 MOISTURE RESISTANCE: IP67 (MATED CONDITION)
- 3.6 MATING CYCLE DURABILITY: 100 CYCLES
- 3.7 RoHS COMPLIANT
- 4. MATING PART: ATP06-2S* PLUG. (* = MODIFICATIONS AND COLORS)
- 5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.
- 6 CONTACT SIZE AND REAR SEAL WIRE RANGE:

CONTACT	MIN. INSUL	MAX. INSUL	TYPICAL
SIZE	O.D.	O.D.	WIRE RANGE
12	3.40 mm (.134 in)	4.95 mm (.195 in)	10 - 14 AWG


PART NUMBER CHART			
COLOR	PART NUMBER		
GREY	ATP04-2P		
BLACK	ATP04-2P-BLK		

STANDARD MOLDED COLOR IS GREY. ADDITIONAL COLOR (BLACK) IS AVAILABLE VIA SPECIAL ORDER.

		REVISIONS			
REV	ECO	DESCRIPTION	DATE	BY	APPR
A3	-	RELEASE NEW DWG FORMAT	18/OCT/13	DRP	-

RECEPTACLE, 2 PIN, ATP SERIES

ATP04-2P-XXX



REFER TO PART NUMBER CHART FOR **AVAILABLE CONNECTOR COLORS**

SEE PART NUMBER CHART DESCRIPTION ITEM PART NUMBER QUANTITY MATERIALS LIST UNLESS OTHERWISE SPECIFIED **Amphenol** SIGNATURES DATE 1) All dimensions are in metric(mm) D.PARKS 18/OCT/13 1 PL DEC ±0.30 | Fractions ±1/64 2 PL DEC ±0.15 3 PL DEC ±0.08 | Angles ±1° Sine Systems - www.amphenol-sine.com 44724 Morley Drive 3) Note reference = X Clinton Township, MI 48036 MATERIAL SPECIFICATIONS: RECEPTACLE, 2 PIN, ATP SERIES THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SIZE PROCESS SPECIFICATIONS: SHOWN HEREON ARE THE PROPERTY OF **A3** В ATP04-2P-XXX THE AMPHENOL CORPORATION. NO RIGHT OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS. NEXT ASS'Y: SCALE: NONE SHEET 1

ATP Series™ - Contact Size 12 Options

Machined Contacts, Sockets & Pins				
Part Number	Description	Size	AWG	Туре
AT60-204-12141-10	Male Contact - Pin, Nickel-plated	12	10-12	Machined
AT62-203-12141-10	Female Contact - Socket, Nickel-plated 12 10-12		Machined	
AT60-220-1231	Male Contact - Pin, Gold-plated 12 12-14 N		Machined	
AT62-210-1231	Female Contact - Socket, Gold-plated	12	12-14	Machined
AT60-204-12141	Male Contact - Pin, Nickel-plated	12	12-14	Machined
AT62-203-12141	Female Contact - Socket, Nickel-plated	12	12-14	Machined

DiagnosticGrade™ Machined Contacts, Sockets & Pins • Smaller AWG for Diagnostic Applications • Gold-plated • Increased Mating Cycles • Cost-effective				
Part Number Description		Size	AWG	Туре
65-54749	Male Contact - DiagnosticGrade™, Pin, Gold-plated	12	20	Machined
AT62-210-1231-1820	Female Contact - DiagnosticGrade™, Socket, Gold-plated	12	20	Machined

Tooling - Machined Contacts			
Part	Part Number	Description	
	CA-5D12	Universal Hand Crimp Tool, Size 12/16/20 (Machined contacts only)	
550	CA-5E12	Pneumatic Crimp Tool, Size 12/16/20 (Machined contacts only)	
0,	M300-25A	Hand Crimp Tool used with Crimp Locator MFX-3966, Size 12, 10AWG (Machined contacts only)	
C	MFX-3966	Contact Locator used with Hand Crimp Tool M300-25A, Size 12, 10AWG (Machined contacts only)	

Contact Removal Tools			
Part	Part Number	Description	
	ATRT-100	Used for removal of contacts for A Series™ products	
	AT11-337-1205	Contact Removal Tool, Plastic, Size 12	
	A114017	Sealing Plug, Size 12, White	

Stamped & Formed Contacts, Sockets & Pins					
Part Number	Description	Size	AWG	Туре	
AT60-12-0244	Male Contact - Pin, Gold-plated	12	10-12	Stamped & Formed	
AT62-12-0244	Female Contact - Socket, Gold-plated	12	10-12	Stamped & Formed	
AT60-12-0222	Male Contact - Pin, Nickel-plated	12	10-12	Stamped & Formed	
AT62-12-0222	Female Contact - Socket, Nickel-plated	12	10-12	Stamped & Formed	
AT60-12-0144	Male Contact - Pin, Gold-plated	12	12-14	Stamped & Formed	
AT62-12-0144	Female Contact - Socket, Gold-plated	12	12-14	Stamped & Formed	
AT60-12-0166	Male Contact - Pin, Nickel-plated	12	12-14	Stamped & Formed	
AT62-12-0166	Female Contact - Socket, Nickel-plated	12	12-14	Stamped & Formed	

Tooling - Stamped & Formed Contacts			
Part	Part Number	Description	
	MFX-3973	Crimp Die - Size 12 (S&F contacts only)	
	MFX-3985	Crimp Die - Svize 12 (S&F contacts only) 10-12AWG -02XX Series	
	ATT-12-00	Hand Crimp Tool - Size 12, 12AWG (S&F contacts only)	
	ATT-12-01	Hand Crimp Tool - Size 12, 10AWG (S&F contacts only)	