

NOTES: UNLESS OTHERWISE SPECIFIED

MATERIAL:

HOUSING: THERMOPLASTIC SEAL: SILICONE RUBBER

- 2. MODIFICATIONS: N/A
- 3. SPECIFICATIONS:
 - 3.1 CURRENT RATING: 25 AMPS
 - 3.2 OPERATING TEMPERATURE: -55°C TO +125°C
 - 3.3 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC. 3.4 INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 25°C.
 - 3.5 MOISTURE RESISTANCE: IP67 (MATED CONDITION)

 - 3.6 MATING CYCLE DURABILITY: 100 CYCLES
 - 3.7 RoHS COMPLIANT
- 4. MATING PART: ATP04-2P* RECEPTACLE. (* = MODIFICATIONS AND COLORS)
- 5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.
- 6 CONTACT SIZE AND REAR SEAL WIRE RANGE:

CONTACT	MIN. INSUL	MAX. INSUL	TYPICAL
SIZE	O.D.	O.D.	WIRE RANGE
12	3.40 mm (.134 in)	4.95 mm (.195 in)	10 - 14 AWG

AMPHENOL ATP06-2S	18.6


PART NUMBER CHART			
COLOR	PART NUMBER		
GREY	ATP06-2S		
BLACK	ATP06-2S-BLK		

STANDARD MOLDED COLOR IS GREY. ADDITIONAL COLOR (BLACK) IS AVAILABLE VIA SPECIAL ORDER.

		REVISIONS			
REV	ECO	DESCRIPTION	DATE	BY	APPR
А3	-	RELEASE NEW DWG FORMAT	18/OCT/13	DRP	-

PLUG, 2 SOCKET, ATP SERIES

· A3



SEE PA	SEE PART NUMBER CHART			
PA	PART NUMBER		DESCRIPTION	ITEM
QUANTITY	MA	TERI	IALS LIST	
UNLESS OTHERWISE SPEC	SIGNATUR	ES DATE	Amphonol	
Tolerances are as follows: 1 PL DEC ±0.30 Fractions	D.PARKS	18/OCT/13	Amphenol	
2 PL DEC ±0.15 Angles ±1 3 PL DEC ±0.08			Sine Systems - www.amphenol-sine.com	
3) Note reference = X	ENGINEER:		44724 Morley Drive	
MATERIAL SPECIFICATIONS:	APPROVAL:		Clinton Township, MI 48036	
	CUSTOMER:		PLUG, 2 SOCKET, ATP SERIES	
PROCESS SPECIFICATIONS:	THIS DRAWING IS SUPPLINFORMATION ONLY. DE			
SPECIFICATIONS AND PERFORMAN SHOWN HEREON ARE THE PROPER! THE AMPHENOL CORPORATION. NO OF REPRODUCTION ARE IMPLIED. A DIMENSIONS ARE SUBJECT TO NOR		HE PROPERTY OF RATION. NO RIGHT: IMPLIED. ALL	4TD00 00 \/\/	A3
NEXT ASS'Y:	MANUFACTURING VARIA		SCALE: NONE SHEET 1 OF	1

REFER TO PART NUMBER CHART FOR

AVAILABLE CONNECTOR COLORS

ATP Series™ - Contact Size 12 Options

	Machined Contacts, Sockets & Pins				
Part Number	Description	Size	AWG	Туре	
AT60-204-12141-10	Male Contact - Pin, Nickel-plated	12	10-12	Machined	
AT62-203-12141-10	Female Contact - Socket, Nickel-plated	12	10-12	Machined	
AT60-220-1231	Male Contact - Pin, Gold-plated	12	12-14	Machined	
AT62-210-1231	Female Contact - Socket, Gold-plated	12	12-14	Machined	
AT60-204-12141	Male Contact - Pin, Nickel-plated	12	12-14	Machined	
AT62-203-12141	Female Contact - Socket, Nickel-plated	12	12-14	Machined	

DiagnosticGrade™ Machined Contacts, Sockets & Pins • Smaller AWG for Diagnostic Applications • Gold-plated • Increased Mating Cycles • Cost-effective				
Part Number Description		Size	AWG	Туре
65-54749	Male Contact - DiagnosticGrade™, Pin, Gold-plated	12	20	Machined
AT62-210-1231-1820	Female Contact - DiagnosticGrade™, Socket, Gold-plated	12	20	Machined

Tooling - Machined Contacts			
Part	Part Number	Description	
	CA-5D12	Universal Hand Crimp Tool, Size 12/16/20 (Machined contacts only)	
550	CA-5E12	Pneumatic Crimp Tool, Size 12/16/20 (Machined contacts only)	
0,	M300-25A	Hand Crimp Tool used with Crimp Locator MFX-3966, Size 12, 10AWG (Machined contacts only)	
C	MFX-3966	Contact Locator used with Hand Crimp Tool M300-25A, Size 12, 10AWG (Machined contacts only)	

Contact Removal Tools			
Part	Part Number	Description	
	ATRT-100	Used for removal of contacts for A Series™ products	
	AT11-337-1205	Contact Removal Tool, Plastic, Size 12	
	A114017	Sealing Plug, Size 12, White	

Stamped & Formed Contacts, Sockets & Pins				
Part Number	Description	Size	AWG	Туре
AT60-12-0244	Male Contact - Pin, Gold-plated	12	10-12	Stamped & Formed
AT62-12-0244	Female Contact - Socket, Gold-plated	12	10-12	Stamped & Formed
AT60-12-0222	Male Contact - Pin, Nickel-plated	12	10-12	Stamped & Formed
AT62-12-0222	Female Contact - Socket, Nickel-plated	12	10-12	Stamped & Formed
AT60-12-0144	Male Contact - Pin, Gold-plated	12	12-14	Stamped & Formed
AT62-12-0144	Female Contact - Socket, Gold-plated	12	12-14	Stamped & Formed
AT60-12-0166	Male Contact - Pin, Nickel-plated	12	12-14	Stamped & Formed
AT62-12-0166	Female Contact - Socket, Nickel-plated	12	12-14	Stamped & Formed

Tooling - Stamped & Formed Contacts			
Part	Part Number	Description	
	MFX-3973	Crimp Die - Size 12 (S&F contacts only)	
	MFX-3985	Crimp Die - Svize 12 (S&F contacts only) 10-12AWG -02XX Series	
	ATT-12-00	Hand Crimp Tool - Size 12, 12AWG (S&F contacts only)	
	ATT-12-01	Hand Crimp Tool - Size 12, 10AWG (S&F contacts only)	