




**SPECIFICATIONS**  
 Current Rating: 1.0 Amps  
 Withstanding Voltage: AC 500V  
 Insulation Resistance: 1000MΩ Min  
 Contact Resistance: 20mΩ Max  
 Operation Temperature: -40° to +105°  
 Insulator Material: Polyester (UL94V-0)  
 Contact Material: Phosphor bronze  
 Standard: PA6T  
 Contact Plating: Gold Flash  
 Max. Processing Temp: 240°C for 30-60 seconds  
 (260°C for 5 seconds)




RECOMMEND P.C.B LAYOUT  
 PCB TOLERANCE: ±0.05 (TOP VIEW)

P/N	PIN	DIM.A	DIM.B
FH1.27-01-01PZD	1	0.00	1.27
FH1.27-01-02PZD	2	1.27	2.54
FH1.27-01-03PZD	3	2.54	3.81
FH1.27-01-04PZD	4	3.81	5.08
FH1.27-01-05PZD	5	5.08	6.35
FH1.27-01-06PZD	6	6.35	7.62
FH1.27-01-07PZD	7	7.62	8.89
FH1.27-01-08PZD	8	8.89	10.16
FH1.27-01-09PZD	9	10.16	11.43
.....	.....	.....	.....
FH1.27-01-50PZD	50	(PIN-1)x1.27	(PIN)x1.27

PART NUMBER DESCRIPTION:

FH1.27-01-NPZD



MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: 1.27FH H4.3 1xNPin 180度 W2.1 U型 PC2.4 6T	
		PAR	FH1.27-01-NPZD
DECIMALS:	ANGLES:	DWN	
X.±0.30	X°±5'	CHKD	
X.X±0.20	X.X°±1'	APVD	
X.XX±0.10	X.XX°±0.5'	SCALE N:A	UNIT:MM
CUSTOMER COPY		SIZE:A4	SHEET:1F1
			REV:A