

03P~12P



02P

**SPECIFICATIONS**

Current Rating: 5A AC,DC  
 Voltage Rating: 250V AC,DC  
 Temperature Range: -25°C ~ +85°C  
 Contact Resistance: 10mΩ Max  
 Insulation Resistance: 1000MΩ Min  
 Withstanding Voltage: 1500V AC/minute  
 Material: Nylon 66,UL94V-2  
 Color: Black

**Ordering Information & Dimensions**

PART NO.	Dimensions	
	A	B
C3030HF-02P	3.00	6.80
C3030HF-03P	6.00	9.80
C3030HF-04P	9.00	12.80
C3030HF-05P	12.00	15.80
C3030HF-06P	15.00	18.80
C3030HF-07P	18.00	21.80
C3030HF-08P	21.00	24.80
C3030HF-09P	24.00	27.80
C3030HF-10P	27.00	30.80
C3030HF-11P	30.00	33.80
C3030HF-12P	33.00	36.80

				JOINT TECH ELECTRONIC IND. CO., LTD. JOY DAY INDUSTRIAL CO., LTD.	
		UNIT	SCALE	SHEET	TITLE:
		mm		1 of 1	3.00mm PITCH HOUSING-RECEPTACLE, SINGLE ROW, MICRO-FIT
		DRAWN BY	APPROVED BY		
		董正一	董正一		
		2002.08.13	2002.08.13		
B2	REVISE	2008.07.16	GENERAL TOLERANCE		DRAW NO. : C3030HF-XP
B1	REVISE	2008.07.01	X. X±0.25	ANGLE±	
B0	NEW RELEASE	2005.12.14	X. XX±0.15		
REV.	DESCRIPTION	DATE	X. XXX±0.05		REV. B2