



SPECIFICATIONS

Current Rating: 5A AC,DC
 Voltage Rating: 250V AC,DC
 Temperature Range: -25°C ~ +85°C
 Contact Resistance: 10mΩ Max
 Insulation Resistance: 1000MΩ Min
 Withstanding Voltage: 1500V AC/minute
 Material: Nylon 66,UL94V-2
 Color: Black

Ordering Information & Dimensions

PART NO.	Dimensions	
	A	B
C3030HM-02P	3.00	6.85
C3030HM-03P	6.00	9.85
C3030HM-04P	9.00	12.85
C3030HM-05P	12.00	15.85
C3030HM-06P	15.00	18.85
C3030HM-07P	18.00	21.85
C3030HM-08P	21.00	24.85
C3030HM-09P	24.00	27.85
C3030HM-10P	27.00	30.85
C3030HM-11P	30.00	33.85
C3030HM-12P	33.00	36.85

					JOINT TECH ELECTRONIC IND. CO., LTD. JOY DAY INDUSTRIAL CO., LTD.	
			UNIT	SCALE	SHEET	TITLE:
			mm		1 of 1	3.00mm PITCH HOUSING-PLUG, SINGLE ROW, MICRO-FIT
			DRAWN BY	APPROVED BY		
			董正一 2003.05.14	董正一 2003.05.14		
			GENERAL TOLERANCE			DRAW NO. : C3030HM-XP
B1	REVISE	2008.07.01	X. X±0.25	ANGLE±		
B0	NEW RELEASE	2005.12.14	X. XX±0.15			
REV.	DESCRIPTION	DATE	X. XXX±0.05			
						REV. B1