



2X01P

**SPECIFICATIONS**

Current Rating: 5A AC,DC  
 Voltage Rating: 250V AC,DC  
 Temperature Range: -25°C ~ +85°C  
 Contact Resistance: 10mΩ Max  
 Insulation Resistance: 1000MΩ Min  
 Withstanding Voltage: 1500V AC/minute  
 Material: Nylon 66,UL94V-2  
 Color: Black

**Ordering Information & Dimensions**

PART NO.	Dimensions	
	A	B
C3030HM-2X01P	---	3.85
C3030HM-2X02P	3.00	6.85
C3030HM-2X03P	6.00	9.85
C3030HM-2X04P	9.00	12.85
C3030HM-2X05P	12.00	15.85
C3030HM-2X06P	15.00	18.85
C3030HM-2X07P	18.00	21.85
C3030HM-2X08P	21.00	24.85
C3030HM-2X09P	24.00	27.85
C3030HM-2X10P	27.00	30.85
C3030HM-2X11P	30.00	33.85
C3030HM-2X12P	33.00	36.85

				UNIT: mm    SCALE: 1 of 1    SHEET: 1 of 1		<b>TITLE:</b> 3.00mm PITCH HOUSING-PLUG, MICRO-FIT
				DRAWN BY: 董正一    APPROVED BY: 董正一 2001.02.01    2001.02.01		
		GENERAL TOLERANCE				
B1	REVISE	2007.04.16	X. X±0.25	ANGLE±		
B0	NEW RELEASE	2005.12.14	X. XX±0.15			
REV.	DESCRIPTION	DATE	X. XXX±0.05			
				DRAW NO.: C3030HM-2XNP		REV. B1