GRT155R61A225ME01# "#" indicates a package specification code.
















< List of part numbers with package codes >

GRT155R61A225ME01D , GRT155R61A225ME01W , GRT155R61A225ME01J

Shape



	W size	0.5 ±0.05mm
	Tsize	0.5 ±0.05mm
	External terminal width e	0.15 to 0.35mm
	Distance between external terminals g	0.3mm min.
	Size code in inch(mm)	0402 (1005M)

Notes

Derating1

References

Packaging	Specifications	Minimum quantity
D	ф180mm Paper taping	10000
J	ф330mm Paper taping	50000
W	φ180mm Paper taping (W8P1*) * Width: 8mm, Pocket pitch: 1mm	20000

Mass (typ.)	Mass (typ.)	
1 piece	1.6mg	
ф180mm Reel	118g	

Specifications

Capacitance	2.2μF ±20%
Rated voltage	10Vdc
Temperature characteristics (complied standard)	X5R(EIA)
Capacitance change rate	±15.0%
Temperature range of temperature characteristics	-55 to 85°C
Operating temperature range	-55 to 85°C

1 of 1



^{1.} This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



^{2.} This datasheet has only typical specifications because there is no space for detailed specifications.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Murata:

GRT155R61A225ME01D