

1.00mm Pitch FFC/FPC – F52Q/F52R Series

RIGHT ANGLE ZIF FLEX CONNECTORS

F52Q/F52R series are 1.00mm pitch right angle ZIF flex connectors with slider mechanism, top contact and surface mount termination. These connectors feature a height of 2.00mm and come in 4 to 34 contacts. This series features a cable thickness of 0.30mm and provide enhanced durability of 30 mating cycles. The connectors come with a robust design and prevent solder and flux wicking. These are ideal for automotive, data, industrial, communication, consumer and medical applications.

- Easy to operate and strong FFC/FPC retention makes it vibration-proof
- Ensures high solderability and high durability



FEATURES

- ZIF (Zero Insertion Force) mechanism
- Slider mechanism
- Design against solder and flux wicking
- High temperature thermoplastic housing
- 4 to 34 contacts available
- Lead and halogen-free

BENEFITS

- Absence of frictional mating wear resulting in high mating cycle life
- Easy to operate and strong FFC/FPC retention makes it vibration-proof
- Ensures high solderability
- Wide operating temperature range of -40°C to +105°C
- Comprehensive range to satisfy different customer requirements
- Meets environmental, health and safety requirements

TECHNICAL INFORMATION

MATERIAL

Housing: LCP, natural color (UL94V-0)

■ Slider: PA9T, black color (UL94V-0)

Contact: Phosphor bronze, T=0.20mm

Anchor-plate: Brass, T=0.20mm

MECHANICAL PERFORMANCE

• FFC/FPC Retention Force: 30gf/pin

Terminal Retention Force: 100gf/terminal

 Anchor-plate Retention Force: 100gf/plate min.

• Durability: 30 mating cycles

ELECTRICAL PERFORMANCE

Voltage Rating: 50V AC/DC

Current Rating: 0.5A

Contact Resistance: 30MΩ max.

• Insulation Resistance: 500M Ω min.

 Dielectric Withstanding Voltage: No short or breakdown after 500V AC, 2mA, 1min.

PACKAGING

- Tape & Reel

APPROVALS AND CERTIFICATIONS

• UL file number E106764

RoHS compliant

SPECIFICATION

Aorora Product Specification: IS.EQC.001

ENVIRONMENTAL

■ Operating Temperature Range: -40°C to +105°C

TARGET MARKETS/APPLICATIONS



Car Multimedia Car Navigation Dashboard PND



Base Station Power Switches



Notebook Tablets Wearables Gaming DSC LCD & PDP TV



Router Server ODD HDD




Sensing element Monitoring camera Human Machine Interface Industrial PC Robotics



Ultrasonic Patient Monitor MRI CT Infusion Pump

PART NUMBER SELECTOR



40R0RAF52Q52R0719EA4