



SPECIFICATIONS

Current Rating: 1.5 Amps
 Insulation Resistance: 1000M Ω Min
 Contact Resistance: 20m Ω Max
 Withstanding Voltage: AC 500V
 Operation Temperature: -40° to +105°
 Contact Material: Brass
 Standard: PA6T
 Insulator Material: Polyester(UL 94V-0)
 Contact Plating: Gold Flash
 Max.Processing Temp: 240°C for 30-60seconds
 (260°C for 5seconds)


| P/N | PIN | DIM.A | DIM.B |
|----------------|-------|-------------|-----------|
| PH2.0-01-01PZD | 1 | 0.00 | 2.00 |
| PH2.0-01-02PZD | 2 | 2.00 | 4.00 |
| PH2.0-01-03PZD | 3 | 4.00 | 6.00 |
| PH2.0-01-04PZD | 4 | 6.00 | 8.00 |
| PH2.0-01-05PZD | 5 | 8.00 | 10.00 |
| PH2.0-01-06PZD | 6 | 10.00 | 12.00 |
| PH2.0-01-07PZD | 7 | 12.00 | 14.00 |
| PH2.0-01-08PZD | 8 | 14.00 | 16.00 |
| PH2.0-01-09PZD | 9 | 16.00 | 18.00 |
| | | | |
| PH2.0-01-40PZD | 40 | (PIN-1)x2.0 | (PIN)x2.0 |



PART NUMBER DESCRIPTION:

PH2.0-01-NPZD

- (D=单排; S=双排)
- (Z=直脚; W=弯脚)
- (PIN数量; 01.....40PIN)
- (排针开关)



RECOMMEND P.C.B LAYOUT
 PCB TOLERANCE: ±0.05 (TOP VIEW)

| | | | |
|---------------------------------------|------------------|---|---|
| MANUFACTURE DWG | | 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd | |
| UNLESS OTHERWISE SPECIFIED TOLERANCES | | | TITLE: 2.0PH H2.0 1xNPin 180 μ PC2.8 PA3.9 PB2.0 L8.7 6T |
| DECIMALS: | ANGLES: | | PAR PH2.0-01-NPZD |
| X. \pm 0.30 | X° \pm 5' | | DWN |
| X.X \pm 0.25 | X.X° \pm 1' | | CHKD |
| X.XX \pm 0.20 | X.XX° \pm 0.5' | APVD | SCALE N:A UNIT:MM |
| CUSTOMER COPY | | SIZE:A4 | SHEET:1F1 REV:A |