



SECTION: A-A



2 Pin






3 Pin

Specifications:

规格:



- Voltage rating: 50V AC/DC
- 额定电压: 50V AC/DC
- Current rating: 1A AC/DC
- 额定电流: 1A AC/DC
- Withstanding voltage: 500V AC/minute
- 耐受电压: 500V AC/分钟
- Temperature range: -25°C~+85°C
- 温度范围: -25°C~+85°C
- Insulation resistance: 100MΩ min
- 绝缘电阻: 100MΩ Min
- Contact resistance: 30mΩ Max
- 接触电阻: 30mΩ Max



4~9 Pin

X1010 H - XX - N0  
 ① ② ③ ④

1. Series No
2. Category: H-Housing
3. Row No. Pin No: XX-02~15P
4. Material: N0-PA66 UL94V-0



10~15 Pin

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	2.00	5.00	2.00	09	8.00	11.00	4.30
03	2.00	5.00	2.00	10	9.00	12.00	6.15
04	3.00	6.00	2.00	11	10.00	13.00	
05	4.00	7.00	3.40	12	11.00	14.00	8.10
06	5.00	8.00	4.30	13	12.00	15.00	
07	6.00	9.00		14	13.00	16.00	
08	7.00	10.00	15	14.00	17.00		

X1010H-XX-N0	PA66	X1010W	X1010T
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

DSND	SCALE: N/A	MODEL TYPE: 1.0mm Crimp Style Connector
DWN	VIEW:	PART NO.: X1010H-XX-N0
CHKD	UNIT: mm/in	DWG NO.: X-X1010H-XX-N0
APPD	SIZE: A4	



XKB INDUSTRIAL PRECISION CO., LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0

广东星坤科技股份有限公司

MARK	DESCRIPTION	DATE	REVISED	APPROVED
Δ建				
Δ数				
ΔX				

REVISIONS	UNSPECIFIED TOLERANCES
ANGLAR ±5°	
L ≤ 4 ±0.2	
4 < L ≤ 16 ±0.3	
16 < L ≤ 63 ±0.4	
L > 63 ±0.5	

文件工程章