


Specifications:
 规格:
 Voltage rating: 50V AC/DC
 额定电压: 50V AC/DC
 Current rating: 1A AC/DC
 额定电流: 1A AC/DC
 Withstanding voltage: 500V AC/minute
 耐受电压: 500V AC/分钟
 Temperature range: -25°C~+85°C
 温度范围: -25°C~+85°C
 Insulation resistance: 100MΩ min
 绝缘电阻: 100MΩ Min
 Contact resistance: 30mΩ Max
 接触电阻: 30mΩ Max

X1010 T - P SN
 ① ② ③ ④

1. Series No
2. Category: T-Terminal
3. Material: P-Phosphor Bronze
4. Plating: SN-Tin Plated
V01: Gold Flash



SEC: A-A

SEC: B-B

SEC: C-C

X1010T-PSN	Phosphor Bronze	AWG#28~32	X1010H
PART NO	Material	Wire Range	Suitable XKB Housing

广东星坤科技股份有限公司

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
Δ*					ANGULAR ±5°
Δx					L ≤ 4 ±0.2
Δx					4 < L ≤ 16 ±0.3
					16 < L ≤ 63 ±0.4
					L > 63 ±0.5



DSND	SCALE: N/A	MODEL TYPE: 1.0mm Crimp Style Connector
DWN	VIEW:	PART NO.: X1010T-PSN
CHKD	UNIT: mm/in	DWG NO.: X-X1010T-PSN
APPD	SIZE: A4	WEIGHT SHEET REVISION
XKB INDUSTRIAL PRECISION CO., LIMITED		1/1 A0

文件工程章