


0.2 [0.008]

Specifications:


规格:
 Voltage rating:50V AC/DC
 额定电压: 50V AC/DC
 Current rating:1.5A AC/DC
 额定电流: 1.5A AC/DC
 Withstanding voltage:500V AC/minute
 耐受电压: 500V AC/分钟
 Temperature range:-40°C-+125°C
 温度范围: -40°C-+125°C
 Insulation resistance:100MΩ min
 绝缘电阻: 100MΩ Min
 Contact resistance:20mΩ Max
 接触电阻: 20mΩ Max

X1256 T - P XX - L
 ① ② ③ ④ ⑤

- 1.Series No
- 2.Category:T-Terminal
- 3.Material:P-Phosphor Bronze
- 4.Plating:V01-Gold Flash
SN-Plated Tin
- 5.Special No:L-Front buckle



SEC:A-A



SEC:B-B

X1256T-PXX-L	Phosphor Bronze	AWG#30~26	X1256H-L
PART NO	Material	Wire Range	Suitable XKB Housing

DSND	SCALE: N/A	MODEL TYPE: 1.25mm Crimp Style Connector
DWN	VIEW:	PART NO.: X1256T-PXX-L
CHKD	UNIT: mm/in	DWG NO.: X-X1256T-PXX-L
APPD	SIZE: A4	WEIGHT SHEET REVISION



XKB INDUSTRIAL PRECISION CO.,LIMITED

1/1 A0

ANGULAR ±5°

Δx	L ≤ 4	±0.2
Δx	4 < L ≤ 16	±0.3
Δx	16 < L ≤ 63	±0.4
MARK	L > 63	±0.5

UNSPECIFIED TOLERANCES