



2~5A

SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Wafer Nylon46, UL94V-0  
PIN Brass Tin-plated

编 号	尺寸 (mm)	
	A	B
A2508-02AW	2.50	7.50
A2508-03AW	5.00	10.00
A2508-04AW	7.50	12.50
A2508-05AW	10.00	15.00
A2508-06AW	12.50	17.50
A2508-07AW	15.00	20.00
A2508-08AW	17.50	22.50
A2508-09AW	20.00	25.00
A2508-10AW	22.50	27.50
A2508-11AW	25.00	30.00
A2508-12AW	27.50	32.50
A2508-20AW	47.50	52.50

PCB LAYOUT

GENERAL TOLERANCE		制图	钱岳生		料号	A2508-nAW		版本	A
X±0.25	X*±2'	DRAWING	2013、07、01		PART NO.	XA-AW		REV.	
.X±0.20	.X*±1'	审核	张名		品名	WAFER DIP TYPE		页次	1/1
.XX±0.15	.XX*±0.5'	CHECK	2013、07、03		TITLE			SHEET	
.XXX±0.10	.XXX*±0.5'	核准	张名		客户料号				
		APPROVAL	2013、07、03		CUTM. NO.				
		单位	MM	比例	深圳市金航标电子有限公司		www.kinghelm.com.cn		
		UNITS		SCALE	KH-A2508-02AW		0755-28190160		