



2~5A

SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
- 4、Contact Resistance: $20\text{m}\Omega$ Max
- 5、Insulation Resistance: $1000\text{M}\Omega$ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Wafer Nylon46, UL94V-0
PIN Brass Tin-plated

编号	尺寸 (mm)	
	A	B
A2508-02A	2.50	7.50
A2508-03A	5.00	10.00
A2508-04A	7.50	12.50
A2508-05A	10.00	15.00
A2508-06A	12.50	17.50
A2508-07A	15.00	20.00
A2508-08A	17.50	22.50
A2508-09A	20.00	25.00
A2508-10A	22.50	27.50
A2508-11A	25.00	30.00
A2508-12A	27.50	32.50
A2508-13A	30.00	35.00
A2508-14A	32.50	37.50
A2508-15A	35.00	40.00
A2508-20A	47.50	52.50

PCB LAYOUT

GENERAL TOLERANCE		制图	钱岳生		料号	A2508-nA		版本	A
X.±0.25	X.*±2'	DRAWING	2013、07、01		PART NO.	XA单排直针		REV.	
.X±0.20	.X*±1'	审核	张名		品名	WAFER DIP TYPE		页次	1/1
.XX±0.15	.XX*±0.5'	CHECK	2013、07、03		客户料号			SHEET	
.XXX±0.10	.XXX*±0.5'	核准	张名		CUTM. NO.				
		APPROVAL	2013、07、03		深圳市金航标电子有限公司		www.kinghelm.com.cn		
		单位	MM	比例	1:1	KH-A2508-02A		0755-28190160	