



2~5A

SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range:  $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
- 4、Contact Resistance:  $20\text{m}\Omega$  Max
- 5、Insulation Resistance:  $1000\text{M}\Omega$  Min
- 6、Withstanding Voltang:  $1000\text{V AC/minute}$
- 7、Material: Wafer Nylon46, UL94V-0  
PIN Brass Tin-plated

| 编 号        | 尺寸 (mm) |       |
|------------|---------|-------|
|            | A       | B     |
| A2508-02AW | 2.50    | 7.50  |
| A2508-03AW | 5.00    | 10.00 |
| A2508-04AW | 7.50    | 12.50 |
| A2508-05AW | 10.00   | 15.00 |
| A2508-06AW | 12.50   | 17.50 |
| A2508-07AW | 15.00   | 20.00 |
| A2508-08AW | 17.50   | 22.50 |
| A2508-09AW | 20.00   | 25.00 |
| A2508-10AW | 22.50   | 27.50 |
| A2508-11AW | 25.00   | 30.00 |
| A2508-12AW | 27.50   | 32.50 |
| A2508-20AW | 47.50   | 52.50 |

PCB LAYOUT

|                   |            |          |            |       |               |                |                     |       |     |
|-------------------|------------|----------|------------|-------|---------------|----------------|---------------------|-------|-----|
| GENERAL TOLERANCE |            | 制图       | 钱岳生        |       | 料号            | A2508-nAW      |                     | 版本    | A   |
| X.±0.25           | X.*±2'     | DRAWING  | 2013、07、01 |       | PART NO.      | XA-AW          |                     | REV.  |     |
| .X±0.20           | .X*±1'     | 审核       | 张名         |       | 品名            | WAFER DIP TYPE |                     | 页次    | 1/1 |
| .XX±0.15          | .XX*±0.5'  | CHECK    | 2013、07、03 |       | TITLE         |                |                     | SHEET |     |
| .XXX±0.10         | .XXX*±0.5' | 核准       | 张名         |       | 客户料号          |                |                     |       |     |
|                   |            | APPROVAL | 2013、07、03 |       | CUTM. NO.     |                |                     |       |     |
|                   |            | 单位       | MM         | 比例    | 深圳市金航标电子有限公司  |                | www.kinghelm.com.cn |       |     |
|                   |            | UNITS    | MM         | SCALE | KH-A2508-06AW |                | 0755-28190160       |       |     |