






SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25°C~+85°C
- 4、Contact Resistance: 30mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material:Housing PA66, UL94V-0

版本 REV.	日期 DATE	ECN NO.	变更内容 DESCRIPTION	制图 DRAWN



编 号	尺寸 (mm)	
	A	B
A2557-2*02Y	2.50	7.50
A2557-2*03Y	5.00	10.00
A2557-2*04Y	7.50	12.50
A2557-2*05Y	10.00	15.00
A2557-2*06Y	12.50	17.50
A2557-2*07Y	15.00	20.00
A2557-2*08Y	17.50	22.50
A2557-2*09Y	20.00	25.00
A2557-2*10Y	22.50	27.50
A2557-2*11Y	25.00	30.00
A2557-2*12Y	27.50	32.50
A2557-2*20Y	47.50	52.50



GENEAL TOLERANCE		制图	钱岳生		料号	A2557-2*02nY		版本	A
X.X±0.25	X.*±2'	DRAWING	2016、09、22		PART NO.	XHD2.5孔座		REV.	1/1
X.XX±0.20		审核	张名		TITLE			SHEET	
X.XXX±0.10		CHECK	2016、09、23		客户料号				
		核准	张名		CUTM. NO.				
		APPROVAL	2016、09、24		深圳市金航标电子有限公司		www.kinghelm.com.cn		
		单位	MM	比例	1:1	KH-A2557-2X06Y		0755-28190160	
		UNITS		SCALE					