



SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25°C~+85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material:Housing:Nylon66, UL94V-0

编 号	尺寸 (mm)	
	A	B
A2508-02Y	2.50	7.50
A2508-03Y	5.00	10.00
A2508-04Y	7.50	12.50
A2508-05Y	10.00	15.00
A2508-06Y	12.50	17.50
A2508-07Y	15.00	20.00
A2508-08Y	17.50	22.50
A2508-09Y	20.00	25.00
A2508-10Y	22.50	27.50
A2508-11Y	25.00	30.00
A2508-12Y	27.50	32.50
A2508-20Y	47.50	52.50

GENERAL TOLERANCE		制图	钱岳生		料号	A2508-NY		版本	A
X.±0.25	X.*±2'	DRAWING	2013、07、01		PART NO.			REV.	
.X±0.20	.X'±1'	审核	张名		品名	XA单排孔座		页次	1/1
.XX±0.15	.XX'±0.5'	CHECK	2013、07、03		TITLE			SHEET	
.XXX±0.10	.XXX'±0.5'	核准	张名		客户料号				
		APPROVAL	2013、07、03		CUTM. NO.				
		单位	MM	比例	1:1	深圳市金航标电子有限公司		www.kinghelm.com.cn	
		UNITS		SCALE		KH-A2508-10Y		0755-28190160	