



SPECIFICATIONS

- 1、Current Rating: 7A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25°C~+85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1500 AC/minute
- 7、Material:Housing:Nylon66, UL94V-0

编 号	尺寸 (mm)	
	A	B
VH-2P-ZK	3.96	8.02
VH-3P-ZK	7.92	11.98
VH-4P-ZK	11.88	15.94
VH-5P-ZK	15.84	19.90
VH-6P-ZK	19.80	23.86
VH-7P-ZK	23.76	27.82
VH-8P-ZK	27.72	31.78
VH-9P-ZK	31.68	35.74
VH-10P-ZK	35.64	39.70
VH-11P-ZK	39.60	43.66
VH-12P-ZK	43.56	47.62

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	钱岳生		料号 PART NO.	版本 REV.	A
			X.±0.25	X.*±2'		2013、07、01	品名 TITLE			
			.X±0.20	.X*±1'		2013、07、03	客户料号 CUTM. NO.			
			.XX±0.15	.XX*±0.5'		2013、07、05	深圳市金航标电子有限公司			
.XXX±0.10	.XXX*±0.5'	单位 UNITS	MM	比例 SCALE	1:1	KH-VH-5P-ZK		www.kinghelm.com.cn		0755-28190160