

PRODUCT-DETAILS

CA4-31E

CA4-31E Auxiliary Contact Block



General Information

Extended Product Type	CA4-31E
Product ID	1SBN010140R1031
EAN	3471523130135
Catalog Description	CA4-31E Auxiliary Contact Block
Long Description	CA4-31E is a 4-pole front mounted auxiliary contact block equipped with screw terminals. CA4-..E version offers terminal assortment matching the marking of 3-pole AF26(Z)(B)..96-30-00, AF40..96-30-11, AFC26..38-30-00, 4-pole AF09(Z)(B)..80-40-00 / AFC09..38-40-00 or AF09(Z)(B)..80-22-00 / AFC09..38-22-00 contactors. CA4-31E is available with 3 N.O. and 1 N.C. instantaneous contacts for standard industrial environments.

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85389099
Product Main Type	Accessories for Block Contactors

Popular Downloads

Instructions and Manuals	1SBC101041M6801
CAD Dimensional Drawing	2CDC001079B0201

Dimensions

Product Net Width	43 mm
Product Net Depth / Length	39.5 mm
Product Net Height	43 mm
Product Net Weight	0.055 kg

Technical

Connecting Capacity Auxiliary Circuit	Flexible with Ferrule 1/2x 0.75 ... 2.5 mm ² Flexible with Insulated Ferrule 2x 0.75 ... 1.5 mm ² Flexible with Insulated Ferrule 1x 0.75 ... 2.5 mm ² Rigid Solid 1/2x 1 ... 2.5 mm ² Rigid Stranded 1/2x 1 ... 2.5 mm ²
Maximum Electrical Switching Frequency	(AC-15) 1200 cycles per hour (DC-13) 900 cycles per hour
Maximum Mechanical Switching Frequency	3600 cycles per hour
Mounted Auxiliary Contacts	3 NO, 1 NC
Mounting Type	Front mounting
Number of Auxiliary Contacts NC	1
Number of Auxiliary Contacts NO	3
Number of Poles	4
Rated Frequency (f)	Auxiliary Circuit 50 / 60 Hz
Rated Impulse Withstand Voltage (U _{imp})	6 kV
Rated Insulation Voltage (U _i)	acc. to IEC 60947-5-1 690 V acc. to UL/CSA 600 V
Rated Operational Current AC-15 (I _θ)	(500 V) 2 A (690 V) 2 A (24 / 127 V) 6 A (220 / 240 V) 4 A (400 / 440 V) 3 A
Rated Operational Current DC-13 (I _θ)	(24 V) 6 A / 144 W (48 V) 2.8 A / 134 W (72 V) 1 A / 72 W (110 V) 0.55 A / 60 W (125 V) 0.55 A / 69 W (220 V) 0.27 A / 60 W (250 V) 0.27 A / 68 W (400 V) 0.15 A / 60 W (500 V) 0.13 A / 65 W (600 V) 0.1 A / 60 W
Rated Operational Voltage	Auxiliary Circuit 690 V
Rated Short-time Withstand Current Low Voltage (I _{cw})	for 0.1 s 140 A for 1 s 100 A
Standards	IEC/EN 60947-5-1, UL 60947-5-1, CSA C22.2 No. 60947-5-1-14
Suitable For	AF09 AF09Z AF16 AF16Z AF26 AF26Z AF30 AF30Z AF38 AF38Z AF40 AF52 AF65 AF80 AF96

AFC09
 AFC16
 AFC26
 AFC30
 AFC38
 AF09B
 AF09ZB
 AF16B
 AF16ZB
 AF26B
 AF26ZB
 AF30B
 AF30ZB
 AF38B
 AF38ZB
 AF40B
 AF52B
 AF65B
 AF80B
 AF96B

Terminal Type	Screw Terminals
Tightening Torque	Auxiliary Circuit 1.2 N·m
Wire Stripping Length	Auxiliary Circuit 10 mm

Technical UL/CSA

Connecting Capacity Auxiliary Circuit UL/CSA	Rigid Solid 1/2x 18-14 AWG Rigid Stranded 1/2x 18-14 AWG
Pilot Duty UL/CSA	A600 Q600
Tightening Torque UL/CSA	Auxiliary Circuit 11 in·lb

Environmental

Conventional Free-air Thermal Current (I_{th})	acc. to IEC 60947-5-1, $\Theta = 40\text{ °C}$ 16 A
Degree of Protection	acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP20
RoHS Information	2CMT2021-006277
WEEE B2C / B2B	Business To Business
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Certificates and Declarations

ABS Certificate	ABS_20-2060694-PDA
BV Certificate	BV_2634H24900C0
CB Certificate	CB_SE-93053
CQC Certificate	CQC2011010304496319 CQC2013010304651497
Declaration of Conformity - CCC	2020980304001258 2020980304001259
Declaration of Conformity - CE	1SBD250007U1000
Declaration of Conformity - UKCA	1SBD250038U1000
DNV Certificate	DNV_TAE00001BV-5
EAC Certificate	EAC_RU C-FR ME77 B03391
GOST Certificate	GOST_POCCFR.ME77.B07175.pdf
LR Certificate	LRS_LR2002723TA-02
RINA Certificate	RINA_ELE084013XG
RMRS Certificate	RMRS_1802703280

UL Certificate

UL-US-L252354-131-82119002-6
UL-CA-L252354-331-82119002-5

UL Listing Card

UL_E252354

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	46 mm
Package Level 1 Depth / Length	46 mm
Package Level 1 Height	46 mm
Package Level 1 Gross Weight	0.055 kg
Package Level 1 EAN	3471523130135
Package Level 2 Units	box 192 piece
Package Level 2 Gross Weight	10.56 kg
Package Level 3 Units	4608 piece

Classifications

eClass	V11.0 : 27371302
E-Number (Finland)	3706512
E-Number (Sweden)	3211423
ETIM 6	EC000041 - Auxiliary contact block
ETIM 7	EC000041 - Auxiliary contact block
ETIM 8	EC000041 - Auxiliary contact block
ETIM 9	EC000041 - Auxiliary contact block
IDEA Granular Category Code (IGCC)	4743 >> Auxiliary contact block
Object Classification Code	K
UNSPSC	39121522

Categories

Low Voltage Products and Systems → Control Products → Contactors → Block Contactors Accessories

