

PRODUCT-DETAILS

# CB1-610R

## CB1-610R Buzzer



### General Information

Extended Product Type	CB1-610R
Product ID	1SFA619600R6101
EAN	7320500556801
Catalog Description	CB1-610R Buzzer
Long Description	<p>The CB1-610R Buzzer is: Compact - Buzzer - Pulsating sound with pulsating light - Red - Illuminated - 24 V</p> <p>This Buzzer is part of ABB's compact range, the most efficient all-in-one solution available, reducing installation time and cost.</p> <p>The compact range has a high level of dust and water resistance.</p>

### Ordering

Minimum Order Quantity	10 piece
Customs Tariff Number	85369001

### Popular Downloads

Data Sheet, Technical Information	1SFC151007C02__
Instructions and Manuals	1SFC151011M0201

## Dimensions

Product Net Width	0.03 m
Product Net Height	0.03 m
Product Net Depth / Length	0.055 m
Product Net Weight	0.021 kg

## Technical

Ambient Air Temperature	Operation -25 ... +70 °C Storage -40 ... +85 °C
Color	Red
Illumination	Illuminated
Function	Pulsating sound with pulsating light
Degree of Protection	Front IP66 Front IP67 Front IP69K Terminals IP20
Enclosure Type NEMA	Type1 Type12 Type13 Type3R Type4 Type4X
Pollution Degree	3
Rated Frequency (f)	50 / 60 Hz
Rated Operational Voltage	Supply Circuit 24 V AC/DC
Sound dB (A)	80 dB
Connecting Capacity	Flexible with Ferrule 1 x 0.75...2.5 mm <sup>2</sup> Flexible with Ferrule 2 x 0.75...2.5 mm <sup>2</sup> Flexible with Insulated Ferrule 1 x 0.75...2.5 mm <sup>2</sup> Flexible with Insulated Ferrule 2 x 0.75...2.5 mm <sup>2</sup> Flexible 1 x 0.75 ... 2.5 mm <sup>2</sup> Flexible 2 x 0.75 ... 2.5 mm <sup>2</sup> Solid 1 x 0.75...2.5 mm <sup>2</sup> Solid 2 x 0.75...2.5 mm <sup>2</sup>
Connection Type	Screw Clamp
Terminal Type	Screw Terminals
Tightening Torque	0.9 N·m
Wire Stripping Length	8 mm

## Technical UL/CSA

Connecting Capacity	1x 18...14 AWG
UL/CSA	2x 18...14 AWG

## Environmental

RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
RoHS Date	635 4
RoHS Information	2CMT2015-005451
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business

## Certificates and Declarations

CB Certificate	CQC_CN_CN50749
CQC Certificate	CQC2003010305054693
cURus Certificate	UL_E496500-20171020
Declaration of Conformity - CCC	2020980305001187
Declaration of Conformity - CE	2CMT2015-005451
Declaration of Conformity - UKCA	2CMT2020-006121
DNV GL Certificate	9AKK107046A3749

## Container Information

Package Level 1 Units	bag 10 piece
Package Level 1 Width	0.05 m
Package Level 1 Depth / Length	0.235 m
Package Level 1 Height	0.125 m
Package Level 1 Gross Weight	0.214 kg
Package Level 1 EAN	7320500401187

## Classifications

Object Classification Code	P
ETIM 6	EC001026 - Acoustic indicator
ETIM 7	EC001026 - Acoustic indicator
ETIM 8	EC001026 - Acoustic indicator
eClass	V11.0 : 27371214
UNSPSC	46171607
IDEA Granular Category Code (IGCC)	7389 >> Buzzers
E-Number (Finland)	2313697
E-Number (Sweden)	3705038

## Categories

Low Voltage Products and Systems → Control Products → Pilot Devices → Compact Range

Medium Voltage Products and Systems → Service → Spares and Consumables → Parts → All Spare Parts (Relays-SWG-CB)

