

PRODUCT-DETAILS

## CR-S024VADC1CRS

CR-S024VADC1CRS Interface relay cpl. 1c/o, A1-A2=24VAC/DC, Output=6A/250VAC



### General Information

Extended Product Type	CR-S024VADC1CRS
Product ID	1SVR405541R3110
EAN	4013614499289
Catalog Description	CR-S024VADC1CRS Interface relay cpl. 1c/o, A1-A2=24VAC/DC, Output=6A/250VAC
Long Description	CR-S024VADC1CRS Interface relay cpl. 1c/o, A1-A2=24VAC/DC, Output=6A/250VAC screw terminals

### Ordering

EAN	4013614499289
Minimum Order Quantity	10 piece
Customs Tariff Number	85364900

### Popular Downloads

Data Sheet, Technical Information	2CDC110004C0210_05
Instructions and Manuals	2CDC117022D0201
CAD Dimensional Drawing	2CDC001079B0201

## Dimensions

Product Net Width	6.3 mm
Product Net Height	76.4 mm
Product Net Depth / Length	88.5 mm
Product Net Weight	0.03 kg

## Technical

Function	Fully assembled interface relay CR-S
Sub-Function	Relay with standard contacts
Rated Control Supply Voltage (U <sub>s</sub> )	24 V AC/DC
Output	1 c/o (SPDT) contact
Output Signal	250 V / 6 A
Terminal Type	Screw Terminals
Rated Operational Current AC-12 (I <sub>e</sub> )	(230 V) 6 A
Rated Operational Current DC-12 (I <sub>e</sub> )	(24 V) 6 A
Rated Operational Current DC-13 (I <sub>e</sub> )	(24 V) 1 A
Degree of Protection	Terminals IP20
Connecting Capacity	Flexible 2.5 mm <sup>2</sup> Rigid 2.5 mm <sup>2</sup>
Tightening Torque	0.5 N·m
Wire Stripping Length	7 mm
Mounting on DIN Rail	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715
Standards	CAN/CSA C22.2 No.14 IEC/EN 63000 IEC/EN 61810-1 IEC/EN 61984 UL 508

## Technical UL/CSA

Connecting Capacity UL/CSA	Flexible 14 AWG Rigid 14 AWG
Tightening Torque UL/CSA	4.42 in·lb

## Environmental

Ambient Air Temperature	Operation -40 ... +70 °C Storage 0 ... +40 °C
RoHS Status	Following EU Directive 2011/65/EU

## Certificates and Declarations

CSA Certificate	CSA_262671-2785865
cURus Certificate	cURus508_E244328
Declaration of Conformity - CE	1SVD982017-0001
Declaration of Conformity - UKCA	1SVD982017-1000
EAC Certificate	EAC_RU_C-DE.ME77.B.00443-19

<b>Container Information</b>	
Package Level 1 Units	box 10 piece
Package Level 1 Width	93 mm
Package Level 1 Depth / Length	66 mm
Package Level 1 Height	81 mm
Package Level 1 Gross Weight	0.32 kg
Package Level 1 EAN	4013614486654

<b>Classifications</b>	
Object Classification Code	K
ETIM 7	EC001437 - Switching relay
ETIM 8	EC001437 - Switching relay
ETIM 9	EC001437 - Switching relay
eClass	V11.0 : 27371601
UNSPSC	39122331
E-Number (Finland)	2712370
E-Number (Sweden)	4001400

<b>Where Used (as part of "kit")</b>		
Identifier	Description	Type
3BHB051245R0001		Kit

### Categories

Low Voltage Products and Systems → Control Products → Electronic Relays and Controls → Interface Relays and Optocouplers  
 Medium Voltage Products and Systems → Service → Spares and Consumables → Parts → All Spare Parts (Relays-SWG-CB)

