















DATE **DESCRIPTION REV** 2012/12/03 1. INITIAL RELEASE 1. REMOVED EMI GASKET FROM TOP, @J16, AND RIGHT SIDE, @E8, VIEWS FOR CLARITY. ADDED EMI GASKET UNCOMPRESSED OVERALL 2013/02/01 DIMENSIONS TO FRONT VIEW, @E16. ADDED FINISHED ASSEMBLY PRINTED PN/DATE CODE, 9.83 REF DIMENSION TO SIDE VIEW, REMOVED EMI GASKET FOR CLARITY, @E8. ADDED BACK VIEW, @E2, ADDED INNER WALL WELD NOTE. REMOVED BELLY ISO VIEW. CAHNGED DIMENSION "9.83 REF" TOP OF CAGE TO "9.98 REF" TOP OF COIN. MOVED MIN PCB THICKNESS NOTE TO RESPECTIVE PCB LAYOUT SHEETS, REMOVED INSERTION FORCE FROM NOTE 2. MOVED OPEN TOP VIEW & CUTOUT DIMENSIONS TO SHEET 2. (SHEET 1) 2. ADDED "REAR LEG OPTIONS" SECTION, @B16. REMOVED CAGES FROM HEATSINK OPTIONS VIEWS & UPDATED TABLES, @J2, J6 & J11. MOVED VIEW FROM I16 TO F10. ADDED ISO VIEW TO IDENTIFY UNDER BELLY GASKET @F4, TOP VIEW OF OPEN TOP & DIMENSIONS @J16. (SHEET 2) 3. ADDED PN'S 747540610, 747540611, 747540613 & 1111110610 ADDING VIEWS AND PN TABLES. ADDED "SFP+" TO TABLES (SHEET 3) 4. REMOVED BASIC TOLERANCE FROM DIMENSION 35.4 TYP, @F8. ADDED MIN PCB THICKNESS NOTE. (SHEET 4) REMOVED BASIC TOLERANCE FROM DIMENSION 35.4 TYP, @F5. ADDED MIN PCB THICKNESS NOTE. (SHEET 5) 5. REMOVED SINGLE SIDED VIEW AND ADDED APPLICATION NOTE TO TOP OF SHEET. (SHEET 6) | 6. CHANGED TOLERANCE ON DIMENSIONS 0.19 TO 0.19 \pm 0.10, @D9 & F9. ADDED CENTER LINES TO BEZELS. REMOVED CUTAWAY 2 & 4 SIDE VIEWS, RENAMED CUTAWAY 3 TO CUTAWAY 2. REMOVED "10.03 TYP" DIMENSIONS FROM SIDE VIEWS. REMOVED "SEE NOTE 1" FROM 10.6 ±0.1 BEZEL OPENING SIZE DIMENSIONS @D10, F10 & K10. REMOVED "SIZE AND" FROM NOTE 1. (SHEET 7) 7. MOVED NOTES TO BOTTOM LEFT CORNER AND INCREASED TEXT HEIGHT. (SHEETS 1, 4, 5 & 7) 2013/02/14 1. ADDED BASIC DIMENSIONS 19.5 @H8, 29.5 @G8 & 39.5 @F8 BACK TO SINGLE SIDED PCB LAYOUT. (SHEET 4) 2. CORRECTED 3D MODEL CHANGING DIMENSION 12.53 TO 12.44 @K1 &F1. (SHEET 7) 3. CHANGED DIMENSION IN TITLE BLOCK TO MM ONLY. (ALL SHEETS) 2014/03/10 1. REMOVED PN/DATE CODE FROM RIGHT VIEW @E9 AND ADDED TO BACK VIEW @E6. (SHEET 1) 2. REPLACED ISO VIEW @E4 WITH RIGHT VIEW WITH PN/DATE CODE. (SHEET 2) 3. ADDED NEW SHEET 3 WITH OPTIONAL GEN 2 UNDER BELLY GASKET VIEWS. (SHEET 3) 4. RENUMBERED 3-8 TO MAKE THE SHEETS TOTAL 9 5. REMOVED ISO VIEW 1111110610 AND REPLACED WITH ISO VIEW 1001150610 @F13 (SHEET 4) 2017/02/27 | 1. REMASTERED FROM SD-1111112-2610 REV D TO 1111122610 PSD ASY REV E IN NX

> THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION GENERAL molex **TOLERANCES** 1:1 (UNLESS SPECIFIED) 207 ANGULAR TOL ± 1.0 MHANUMAPPARE 2017/02/27 1X6 SFP+ CAGE.120 INCH 4 PLACES PRESS FIT, HEAT SINK, ELASTOMERIC GASKET 3 PLACES DSUN15 2017/04/27 2 PLACES PRODUCT CUSTOMER DRAWING 1 PLACE ± 0.25 RCHEN08 2017/05/03 SERIES 0 PLACES THIRD ANGLE PROJECTION SEE SHEET 4 **GENERAL MARKET** DRAFT WHERE APPLICABLE MUST REMAIN DOCUMENT NUMBER DOC TYPE DOC PART SHEET NUMBER WITHIN DIMENSIONS 9 OF 9 PSD ASY 1111122610

RELEASE STATUS | P1 | RELEASE DATE | 03.05.2017 06:33:50

10

11

9

8

5

12







