



Part Number : [734151692](#)

Product Description : 50 Ohms, MCX Vertical Surface Mount Jack Receptacle, 0.02µm Gold (Au) Plated Body, Tape and Reel

Series Number : 73415

Status : Active

Product Category : RF / Coaxial Connectors



Documents & Resources

Drawings

[Drawing 734151692_sd.pdf](#)

3D Models and Design Files

[3D Model 734151692_stp.zip](#)


[3D Model PDF 734151692.pdf](#)

Specifications

[Product Specification PS-89675-183-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73415
Description	50 Ohms, MCX Vertical Surface Mount Jack Receptacle, 0.02µm Gold (Au) Plated Body, Tape and Reel
Product Family	MCX RF Connectors
Product Name	MCX
Style	PCB
Type	Microminiature
UPC	800755980912

Electrical

Frequency	6 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 335 Vrms@Sea Level

Physical

Gender	Jack
Keying to Mating Part	None
Net Weight	0.509/g
Orientation	Straight
Packaging Type	Embossed Tape on Reel
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	Surface Mount
Reverse Polar	No
Wire/Cable Type	N/A

Solder Process Data

Max-Duration	10
Lead-Free Process Capability	REFLOW
Max-Cycle	2
Max-Temp	260

This document was generated on Aug 25, 2023