






ROHS



PCB layout pattern Side Circuit Diagram

LED colour(LED颜色)	Part No. (料号)
White(白色)	K6-6275D01
Red(红色)	K6-6275D02
Blue(蓝色)	K6-6275D03
Green(绿色)	K6-6275D04
Yellow(黄色)	K6-6275D05
Orange(橙色)	K6-6275D06



Typical Specifications

1. Rating : DC 12V 50mA
2. Operating Force : 250 ± 50 gf
3. Contact Resistance : 100mΩMAX
4. Life : 100,000 Cycles Min

②	Terminal	—	Phosphor bronze	Ag Plating	—	
①	Housing	—	Nylon	Black	—	
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
APPROVALS		DATE		 ELECTRONICS CO.,LTD		
DRAWN	JIANKUN.LU	2015/05/25				
CHECKED				TITLE:	LED Tact Switch	
APPROVALS				PART NO.	K6-6275D	
TOLERANCES ARE	30~øL	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ:
	10~30	±0.20				
	5~10	±0.15	±2'	DRAWING NO.		SHEET 1 OF 1
	~ 5	±0.10				

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			