



NOTE:

- 1.Rating: DC 12V 10mA.
- 2.Dielectric withstanding : AC 110V for 1minute.
- 3.Contact resistance : 1Ω Max.
- 4.Insulation Resistance : 50mΩ Min.
- 5.Operating Force: 110gf±30gf.
- 6.Mechanical Life: 3,000,000 CYCLES.

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑥	Spring	—	1	SUS	Natural	—
⑤	Contact	—	1	SUS	Natural	—
④	Terminal	—	2	Brass	Plating silver	—
③	Knob	—	1	POM	Green	—
②	Cover	—	1	POM	Black	—
①	Base	—	1	POM	Black	—

APPROVALS		DATE		 ELECTRONICS CO.,LTD													
DRAWN	LIUCAN	2021.01.12					TITLE:	PUSHBUTTON SWITCHS									
CHECKED				PART NO.	K8-1613D												
APPROVALS				TOLERANCES ARE	<table border="1"> <tr> <td>30~以上</td> <td>±0.30</td> <td rowspan="4">ANGLE</td> <td rowspan="4">UNIT: mm</td> <td rowspan="4">SCALE: 1:1</td> <td rowspan="4">PROJ: </td> </tr> <tr> <td>10~30</td> <td>±0.20</td> </tr> <tr> <td>5~10</td> <td>±0.15</td> </tr> <tr> <td>~ 5</td> <td>±0.10</td> </tr> </table>	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ:	10~30	±0.20	5~10	±0.15	~ 5	±0.10
30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ:												
10~30	±0.20																
5~10	±0.15																
~ 5	±0.10																
				DRAWING NO.													
				SHEET 1 OF 1													

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
—	A	—	NEW	—	—	—