






ROHS



RECOMMENDED P.C.B. LAYOUT

规格说明: Specifications:

电气特性: Electrical:

1. 额定电流: Current Rating
3.1A/contact terminal
2. 额定电压: Voltage Rating
30V DC
3. 接触阻抗: Contact Resistance
30 milliohms MAX
4. 耐压: Dielectric Withstanding Voltage:
500 V AC AT Sea Level
5. 绝缘阻抗: Insulation Resistance:
1000MEGA ohms MIN

物理性能: Mechanical:

1. 插拔力: Connector Mate and Unmate Force
Mate force: 3.57kgf(MAX)
Unmate force: 1.02kgf(MIN)
2. 端子保持力: Terminal Retention
1.0kgf(MIN)

PART NO	外壳
U-A-24DS-W-2	铁壳
U-A-24DS-W-2T	铜壳

③	Base	—	1	PA9T	White/black
②	Terminal	—	4	Phosphor Bronze	Ag Plated
①	Housing	—	1	SPCC/Copper	Ni Plated
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING

APPROVALS		DATE		 ELECTRONICS CO.,LTD											
DRAWN	JIANKUN.LU	2018.08.01					TITLE:	USB CONNECTOR							
CHECKED				APPROVALS	PART NO.										
APPROVALS				TOLERANCES ARE	ANGLE										
ECN NO.		REV.		DATE.		NEW		DESCRIPTION.		CHANGE.		CHECK.		APPRO.	
30~以上		±0.30		ANGLE		UNIT: mm		SCALE: 1:1		PROJ:		DRAWING NO.		SHEET 1 OF 1	
10~30		±0.25		±2'		DRAWING NO.		SCALE: 1:1		PROJ:		DRAWING NO.		SHEET 1 OF 1	
5~10		±0.20				DRAWING NO.		SCALE: 1:1		PROJ:		DRAWING NO.		SHEET 1 OF 1	
~ 5		±0.15				DRAWING NO.		SCALE: 1:1		PROJ:		DRAWING NO.		SHEET 1 OF 1	

APPROVALS		DATE		 ELECTRONICS CO.,LTD											
DRAWN	JIANKUN.LU	2018.08.01					TITLE:	USB CONNECTOR							
CHECKED				APPROVALS	PART NO.										
APPROVALS				TOLERANCES ARE	ANGLE										
30~以上		±0.30		ANGLE		UNIT: mm		SCALE: 1:1		PROJ:		DRAWING NO.		SHEET 1 OF 1	
10~30		±0.25		±2'		DRAWING NO.		SCALE: 1:1		PROJ:		DRAWING NO.		SHEET 1 OF 1	
5~10		±0.20				DRAWING NO.		SCALE: 1:1		PROJ:		DRAWING NO.		SHEET 1 OF 1	
~ 5		±0.15				DRAWING NO.		SCALE: 1:1		PROJ:		DRAWING NO.		SHEET 1 OF 1	