



SPECIFICATIONS

Material: Insulator: Glass filled PA6T (UL94V-0), Black Contacts: Brass
 Plating: Au or Sn over 50u'
 Ni Electrical Characteristics:
 Contact Resistance: 20m Max. Insulator Resistance: 1000MQ Min. Withstanding Voltage: AC 500v Currnt Rating: 1 AMP
 Operating Temperature: -40 to +105



PCB LAYOUT

未注公差按公差分段要求

Position Dimension	1 Thru 50
A±0.30	1.27 * No. of Positions+0.4
B±0.20	1.27 * No. of Contacts-1.27

—		new		2015/5/3	A		
ECN BO.		DESCRIPTION.		DATE.	REV.		
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	A1254WVS-8P-M	UNLESS OTHERWISE SPECIFIED, TOLERANCE:	X. ±0.25	
			MODEL NAME	A1254WVS-8P-M		X.x ±0.20	
			3RD ANGLE PROJ	HANYONES TECH CO.,LTD		X.xx ±0.15	
						ANGULAR ±3'	
						FILE. NO.	