


SPECIFICATION


- STEM HEIGHT
 1. RATING: DC 12V 50mA.
 2. TRAVE: 0.25 ± 0.1mm.
 3. CONTACT RESISTANCE: 100mΩ MAX.
 4. BOUNCE: 10m SES MAX.

MODEL	OPERATING FORCE	LIFE CYCLES
	180 ± 50gf	100,000 CYCLE
	260 ± 50gf	50,000 CYCLE

CIRCUIT DIAGRAM



P. C. B MOUNTING HOLES



PACKING REEL TYPE

1,000/1REEL (EA)

1,000/1REEL (EA)

		new		2015/5/3	A	
ECN BO.		DESCRIPTION.		DATE.	REV.	
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2		SCALE: 3:1
Mikey	Tom	Jerry	PART NAME	TS-1102S2605090	UNLESS OTHERWISE SPECIFIED, TOLERANCE:	X. ±0.25
			MODEL NAME	TS-1102S2605090		X.x ±0.20
			3RD ANGLE PROJ	HANYONES TECH CO.,LTD		X.xx ±0.15
						ANGULAR ±3'
						FILE NO.