




Circuit Diagram



P.C.B Mounting
pattern Dimension



Specification

1. Rating : 50mA, DC12V Max.
2. Contact resistance : 100mΩ Max.
3. Bounce : 10m sec Max.
4. Travel : 0.3±0.1mm.
5. 力度260g

		new		2015/5/3	A			
ECN BO.		DESCRIPTION.		DATE.	REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2		SCALE: 3:1		
Mikey	Tom	Jerry	PART NAME	TS-115826050	UNLESS OTHERWISE SPECIFIED, TOLERANCE:		X	±0.25
			MODEL NAME	TS-115826050			X.x	±0.20
			3RD ANGLE PROJ	HANYONES TECH CO.,LTD			X.xx	±0.15
							ANGULAR	±3'
							FILE NO.	