


Kinghelm®

REVISED			
REV. NUMBER	DESCRIPTION	DWN	CHK
A	DESIGN		

80±5mm



- NOTES:
- ELECTRICAL:
 - VOLTAGE RATING: 60V AC RMS.
 - FREQUENCY RANGE: DC-3GHz
 - VSWR: 1.3 MAX.
 - CHARACTERISTIC IMPEDANCE: 50 OHMS
 - MATERIAL SEE TABLE:
 - ALL COMPONENTS ARE ROHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
①	线材	1.37黑色同轴线, OD:1.37	AS
②	端子	高仿 1.37 一代端子, 镀金	2

深圳市金航标电子有限公司
www.kinghelm.com.cn
型号: KHA(RG1.37)-TX80B-IPEX 0755-83044319

ALL DIMENSION ARE IN MM		DRAWN		DATE		TITLE	
ENG.	Ellis	Jamy	2018 /06/22	2018 /06/22	一代端子, 同向, 线长80MM		
MFG.	Align		2018 /06/22				
Q.A.	Jeff		2018 /06/22				

COMPUTER GENERATED
DO NOT SCALE
THIS DRAWING

PROJECTION

GENERAL TOLERANCE FOR ANGLES X.X X.XX X.XXX ±1° ±0.3 ±0.25 ±0.150

SIZE Number

SCALE: Free

TYPE

SHEET OF 1

REV A

CUSTOMER P/N:

4 3 2 1