


Kinghelm®

REVISIONS					
REV	NUMBER	DESCRIPTION	DWN	CHK	DATE
A		DESIGN			



同向

NOTES:

1. ELECTRICAL:
 - 1.1. VOLTAGE RATING: 60V AC RMS.
 - 1.2. FREQUENCY RANGE: DC 3GHZ
 - 1.3. VSWR: 1.3 MAX.
 - 1.4. CHARACTERISTIC IMPEDANCE: 50 OHMS
2. MATERIAL SEE TABLE:
3. ALL COMPONENTS ARE RoHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
②	端子	高仿 1.13 4代端子, 镀金	2
①	线材	1.13黑色同轴线, OD:1.13	AS

深圳市金航标电子有限公司		www.kinghelm.com.cn	
KH-113-TX160B-IPEX4		0755-83044319	
ALL DIMENSION ARE IN MM	DRAWN	Jamy	DATE 12/13
	ENG.	Ellis	12/13
COMPUTER GENERATED IN SOLIDWORKS DO NOT SCALE THIS DRAWING	MFG.	Alan	12/13
	Q.A.	Jeff	12/13
PROJECTION			GENERAL TOLERANCE FOR ANGLES X.X X.XX X.XXX ±1' ±0.3 ±0.25 ±0.150
CUSTOMER P/N:		SCALE: Free	TYPE
		SHEET 1 OF 1	

D

D

C

C

B

B

A

A

4

3

2

1

4

3

2

1