



Specifications:

规格:  
 Voltage rating:400V AC/DC  
 额定电压: 400V AC/DC  
 Current rating:10A AC/DC  
 额定电流: 10A AC/DC  
 Withstanding voltage:1800V AC/minute  
 耐受电压: 1800V AC/分钟  
 Temperature range:-40℃-+105℃  
 温度范围: -40℃-+105℃  
 Insulation resistance:100MΩ min  
 绝缘电阻: 100MΩ Min  
 Contact resistance:10mΩ Max  
 接触电阻: 10mΩ Max

X2513 T - H SN - X

① ② ③ ④ ⑤

1. Series No
2. Category:T-Terminal
3. Material:H-High conductivity copper alloy
4. Plating Category:V01-Gold Flash;  
SN-Bright Tin Plating
5. Special No:H-High foot for #20~22AWG  
L-Low foot for #24~26AWG

PART No	Wire range	DIM.A	DIM.B	DIM.C	DIM.D
X2513T-HSN-H	#20~#22	1.50	2.15	2.00	2.15
X2513T-HSN-L	#24~#26	1.40	2.15	2.00	1.45

X2513T-HSN-X	High conductivity copper alloy	#20~#26	X2513H
PART NO	Material	Wire range	Suitable XKB Housing

DSND		SCALE: N/A	MODEL TYPE: 2.50mm Crimp Style Connector
DWN		VIEW:	PART NO.: X2513T-HSN-X
CHKD		UNIT: mm/in	DWG NO.: X-X2513T-HSN-X
APPD		SIZE: A4	WEIGHT
			SHEET
			REVISION
			1/1
			A0

**XKB**

XKB INDUSTRIAL PRECISION CO., LIMITED

MARK	DESCRIPTION	DATE	REVISED	APPROVED	ANGLAR	±5°
Δx					L ≤ 4	±0.2
Δx					4 < L ≤ 16	±0.3
Δx					16 < L ≤ 63	±0.4
					L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						