


Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



NOTE
 MATERIAL & FINISH
 INSULATOR: PA9T 30%GF (UL94 V-0)
 CONTACT: BRASS, GOLD OR TIN OVER NI

ELECTRICAL & MECHANICAL
 CURRENT RATING: 1.5A
 CONTACT RESISTANCE: 20mΩ MAX.
 INSULATION RESISTANCE: 1000MΩ MIN.
 WITHSTAND VOLTAGE: 500V AC/DC
 OPERATION TEMPERATURE: -40°C TO +105°C

new		2015/5/3		A		瀚源	
ECN NO.		DESCRIPTION.		DATE.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	HY2005WV-N-2xXXP	UNLESS OTHERWISE SPECIFIED, TOLERANCE:	X.	±0.25
			MODEL NAME	HY2005WV-N-2xXXP		X.x	±0.20
			3RD ANGLE PROJ	HanElectricity Co.,LTD		X.xx	±0.15
HanElectricity Co.,LTD						FILE.NO.	